


Jan.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES: 1 APPLICABLE CABLE

VINYL SEATH	(Ø5)	DRAIN WIRE	INSULATOR OUTER DIAMETER	0.90 TO 1.00 DIA.
FILLER		WIRE	CONDUCTOR SIZE (STRANDED)	AWG26~27 OR EQUIVALET
CONDUCTOR		INSULATOR	VINYL SEATH OUTER DIAMETER	Ø5.0 *(1)
		SHIELD	DRAIN WIRE	AWG 25 OR EQUIVALENT 7/0.18 DIA. *(2)

- *(1)CABLE ENTRY IS 5.6 MIN.
- *(2)CONSTRUCTION IS FOR REFERENCE.
- 2 THE DIMENSION IN PARENTHESIS IS FOR REFERENCE.

1	POLYCARBONATE	TRANSPARENCY	3	BRASS	UNDER :COPPER PLATING 0.5µm min OVER :TIN REFLOW PLATING 1µm min	△1△2			
2	PHOSPHOR BRONZE				UNDER :NICKEL PLATING 2µm min OVER :GOLD PLATING 1.27µm min	△			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS				
UNITS	mm	SCALE	4 : 1	COUNT	3	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
						DIS-E-003517	YH. MAMADA	YH. ENAMI	10.11.26
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : HO. MIWA	05.01.05	DRAWING NO.		EDC3-120679-05			
		CHECKED : TH. KAMEYA	05.01.05	PART NO.		TM11AP-88P(21)			
		DESIGNED : SS. SATOH	05.01.05	CODE NO.		CL222-2780-6-21			
		DRAWN : SS. SATOH	05.01.05			△1△2			