


Sep. 1. 2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO 70 °C			STORAGE TEMPERATURE RANGE	— °C TO — °C			
	VOLTAGE	AC 125 V			OPERATING HUMIDITY RANGE	— % TO — %			
	CURRENT	0.5 A			APPLICABLE CABLE	—			
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			×	×
MARKING		CONFIRMED VISUALLY.						×	×
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE		1 mA (DC OR 1000 Hz).			① >40 mΩ MAX.			×	×
INSULATION RESISTANCE		100 V DC.			250 MΩ MIN.			×	×
VOLTAGE PROOF		300 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.			×	×
MECHANICAL CHARACTERISTICS									
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE 40 N MAX. EXTRACTION FORCE 4 N MIN.			×	—
MECHANICAL OPERATION		3000 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 60 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.			×	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 10 μs.			×	—
SHOCK		490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 6 DIRECTIONS.			② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.			×	—
LOCKING FORCE		PULL THE CONNECTOR, CABLE AXIALLY.			40 N MIN.			×	—
ENVIRONMENTAL CHARACTERISTICS									
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → 5~35 → 85 → 5~35 °C TIME 30 → 2~3 → 30 → 2~3 min UNDER 5 CYCLES.			NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.			×	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 60 °C, 90~95 %, 96 h.			① INSULATION RESISTANCE: AT HIGH HUMIDITY : 1 MΩ MIN. AT DRY : 100 MΩ MIN. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.			×	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION INCLUDING DAMAGE OF CONNECTOR FUNCTION.			×	—
SOLDERING CONDITION								×	—
REMARKS					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
① CONTACT RESISTANCE EXCLUDES BULK RESISTANCE.					H. Ando	H. Ando	N. Miyajima	<i>[Signature]</i>	
Unless otherwise specified, refer to JIS C 5402.					'06.05.10	'06.05.10	'06.05.10	'06.5.10	
Note QT:Qualification Test AT:Assurance Test ×:Applicable Test									
HRS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO. 3 2 6 0 - 8 S 3 (5 5)		
CODE NO.(OLD)		DRAWING NO. E L C 4 - 0 4 6 5 8 6 - 0 2			CODE NO. C L 2 3 2 - 0 0 1 0 - 5 - 5 5			1 / 1	