


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


HRS DRAWING FOR REFERENCE






Recommended PCB Layout (t=1.6 FR4) Land/Pad Part Resist Part









Note 1. ※ indicates duplicate dimension.
2. This pattern is an example of the FCB.
(thickness=1.6mm, material=FR4, layer thickness containing plating=0.035mm)


Reference:Panel Layout(Thickness 0.5~2.5mm)




Assembled figure (1:1)




Nut (1:1)




Washer (1:1)



Packing specification(FREE)





Packing unit:max 250pcs/box
(Max 4 trays /box)

Max 70pcs/tray
(There is some fraction trays)

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	BERYLLIUM COPPER	GOLD PLATING			
2	SPS		5	PHOSPHOR BRONZE	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	4	BRASS	NICKEL PLATING

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△0					

HIROSE ELECTRIC CO., LTD.

APPROVED	TO. KATAYAMA	18. 03. 05
CHECKED	TO. KATAYAMA	18. 03. 05
DESIGNED	MA. SAEKI	18. 03. 05
DRAWN	MA. SAEKI	18. 03. 05

DRAWING NO.	EDC-368216-01-00
PART NO.	BNC(75)-BLR-PC-12G(01)
CODE NO.	CL302-0081-0-01 △0 1/1