

APPLICABLE STANDARD						
RATING	VOLTAGE	150V AC	CURRENT	1A		
	OPERATING TEMPERATURE RANGE	-35°C TO + 85°C (NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C (NOTE 3)		
	OPERATING HUMIDITY RANGE	20% TO 80% (NOTE 2)	STORAGE HUMIDITY RANGE	20% TO 70% (NOTE 3)		
	APPLICABLE CONNECTOR	DF13-*S-1.25C	APPLAICABLE CRIMP CONTACT	DF13-2630SCF, DF13-3032SCF		
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		100m A (DC OR 1000 Hz).		30mΩ MAX.	X	—
INSULATION RESISTANCE		100V DC.		500MΩ MIN.	X	—
VOLTAGE PROOF		500V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		30TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 5 TO 35→+85→ 5 TO 35 °C TIME 30→ 5 TO 15 → 30→ 5 TO 15 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 500MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 500MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RESISTANCE TO SOLDERING HEAT		1) FLOW SOLDERING 250±5°C MAX. FOR 3 SECONDS. 2) SOLDERING IRONS: 290±10°C, FOR 3 SECONDS		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 215±5°C FOR INSERTION DURATION, 3 SECONDS.		SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSUED.	X	—
REMARKS						
NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT.						
NOTE 2: NO CONDENSING.						
NOTE 3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD AFTER PCBBOARD , OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERM STORAGE DURING TRANSPORTATION.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
⚠						
Unless otherwise specifid , refer to JIS C 5402.			APPROVED	TY.OMA	06.09.25	
			CHECKED	HK.UMEHARA	06.09.25	
			DESIGNED	TS.KUMAZAWA	06.09.25	
			DRAWN	AK.MIURA	06.09.21	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-162420-03	
HRS	SPECIFICATION SHEET		PART NO.	DF13-*P-1.25DS (20)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL536	⚠	1/1