




Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




DRAWING FOR REFERENCE
This is subject to change without notice


- NOTE
- 1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
 - 2. CONTACT PLATING SPECIFICATIONS.
CONTACT AREA : GOLD 0.05 μ m MIN.
SMT LEAD : GOLD 0.05 μ m MIN.
UNDER PLATING : NICKEL 1 μ m MIN.
(SURFACE : SEALING)
 - 3. METAL FITTING PLATING SPECIFICATIONS.
SMT LEAD : GOLD 0.05 μ m MIN.
UNDERPLATING : NICKEL 1 μ m MIN.
(SURFACE : SEALING)
 - 4. HRS MARK AND CAV No. ARE INDICATED IN APPROX POSITION SHOWN.
 - 5. A PART OF THE WALL COULD BE NOTCHED.




A-A (50:1)




ENGAGEMENT FIGURE (50:1)



	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
△						. . .	△						. . .
△						. . .	△						. . .
△						. . .	△						. . .


4	PS	CLEAR (EMBOSSED CARRIER TAPE)								
3	COPPER ALLOY	3		7	PS	CLEAR (REINFORCEMENT COLLAR)				
2	COPPER ALLOY	2		6	PS	BLACK (PLASTIC REEL)				
1	LCP	UL94 V-0, BLACK		5	POLYESTER	CLEAR (COVER TAPE)				
NO.	MATERIAL	FINISH , REMARKS			NO.	MATERIAL	FINISH , REMARKS			
REMARKS						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
						S. H. JUNG 17. 05. 08	S. H. JUNG 17. 05. 08	H. W. JO 17. 05. 08	T. S. KANG 17. 05. 08	17. 05. 08
CODE NO. (OLD)			DRAWING NO. EDC3-631850			PART NO. BM23FR0.6-20DP-0.35V(895)				
		SCALE 10:1								
		UNITS mm	HRS HIROSE KOREA CO., LTD.			CODE NO CL 6644-0009-9-895				

7 RECOMMENDED PCB LAYOUT




RECOMMENDED METAL MASK DIMENSIONS

METAL MASK THICKNESS : $100 \mu\text{m}$



6 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.



REFLOW METHOD: N2 REFLOW

NUMBER OF REFLOW CYCLES: 2 CYCLES MAX.

1) REFLOW TIME

DURATION ABOVE 220°C , 60 SEC MAX.

(PEAK TEMPERATURE: 250°C MAX)

2) PRE-HEAT TIME

PRE-HEAT TEMPERATURE(MIN): 150°C

PRE-HEAT TEMPERATURE(MAX): 180°C

PRE-HEAT TIME: 90-120 SEC.

6 THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDITIONAL FACTORS, SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.

7 PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.

	DRAWING NO.	EDC3-631850	PART NO.	BM23FR0.6-20DP-0.35V(895)
	SCALE	10:1	CODE NO	CL 6644-0009-9-895
	UNITS	mm		2/3

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

