





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Notes 1. Lead Co-planarity include reinforced metal fittings shall be 0.1 mm MAX.
2 When this connector mates with DF14-25S-1.25C, the mating length is 7.3 mm.

			6	Polyester	Black(Reel)
2	Brass	Contact area: Gold plating 0.1 μm MIN Lead area: Tin-Copper plating 1 μm MIN Under plating: Nickel plating 1 μm MIN	5	Polyester	CLEAR(Cover Tape)
			4	PS	CLEAR(Embossed Carrier Tape)
			3	Phosphor bronze	Lead area: Tin-Copper plating 1 μm MIN Under plating: Nickel plating 0.5 μm MIN
1	Polyamide	Beige , UL94V-0			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA		16. 05. 30	DRAWING NO.	EDC-160525-83-00		
		CHECKED : TS. FUKUSHIMA		16. 05. 30	PART NO.	DF14A-25P-1. 25H(83)		
		DESIGNED : HT. SATO		16. 05. 30	CODE NO.	CL538-0124-7-83		
		DRAWN : HK. HAYASHI		16. 05. 30				
							1/	

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

