

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
APPLICABLE STANDARD											
RATING	Operating Temperature Range		-55°C to 105°C (Note1)			Storage Temperature Range		-10°C to +60°C (Note3)			
	Operating Humidity Range		20% to 80% (Note2)			Storage Humidity Range		40% to 70% (Note3)			
	Applicable Connector		DF51K-16DS-2C(###)			Current	AWG 30 : 0.5A AWG 28 : 1A AWG 26 : 1.5A AWG 22-24 : 2A				
	Voltage		250V AC/DC								
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENTS			QT	AT	
CONSTRUCTION											
General Examination		Visually and by measuring instrument.				According to drawing.			O	O	
Marking		Confirmed visually.							O	O	
ELECTRICAL CHARACTERISTICS											
Contact Resistance		20mV MAX, 1mA (DC or 1000Hz).				30 mΩ MAX.			O	-	
Millivolt Level Method											
Insulation Resistance		500 V DC.				1,000 MΩ MIN.			O	-	
Voltage Proof		650 V AC for 1 min.				No flashover or breakdown.			O	-	
MECHANICAL CHARACTERISTICS											
Mechanical Operation (Sn Plating)		30 times insertion and extraction.				①Contact resistance: 30mΩ MAX ②No damage, crack or looseness of parts.			O	-	
Mechanical Operation (Au Plating)		50 times insertion and extraction.				①Contact resistance: 30mΩ MAX ②No damage, crack or looseness of parts.			O	-	
Mating and unmating force (Sn Plating)		It takes out and inserts with a conformity connector.				①Insertion Force: 72.2N MAX ②Extraction Force : 4.2N MIN			O	-	
Mating and unmating force (Au Plating)		It takes out and inserts with a conformity connector.				①Insertion Force: 46.2N MAX ②Extraction Force: 4.0N MIN			O	-	
Vibration		Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.				①No electrical discontinuity of 1 μ s. ②No damage, crack or looseness of parts.			O	-	
Shock		Acceleration 490 m/s ² duration of pulse 11 ms at 3 times for 3 directions.							O	-	
ENVIRONMENTAL CHARACTERISTICS											
Damp Heat (Steady State)		Exposed at 40 ± 2 °C , humidity 90 to 95 %, 96 h. (After leaving the room temperature for 1 to 2h.)				①Contact resistance: 30 mΩ MAX. ②Insulation resistance: 500MΩ MIN. ③No damage, crack or looseness of parts.			O	-	
Remarks Note 1: Include the temperature rising by current. Note 2: No condensing Note 3: Apply to the condition of long term storage for unused products before pcb on board, after pcb board , operating temperature and humidity range is applied for interim storage during transportation.											
					DRAWN J.S CHOI 18.03.02	DESIGNED J.S CHOI 18.03.02	CHECKED S.M.LIM 18.03.02	APPROVED T.S KANG 18.03.02	RELEASED ENG 20. 02. 13 DEPT		
Unless otherwise specified, refer to IEC 60512.											
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST											
HIROSE KOREA CO.,LTD.			SPECIFICATION SHEET				PART NO. DF51K-16DP-2DS(800)				
CODE NO.(OLD) CL		DRAWING NO. ELC4-632482			CODE NO. CL 6652-0052-2-800					1/2	

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Rapid Change of Temperature	Temperature -55 °C → +105 °C Time 30min → 30min Under 5 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)	①Contact resistance: 30 mΩ MAX. ②Insulation resistance: 1,000MΩ MIN. ③No damage, crack or looseness of parts.	O	—
Dry Heat	Exposed at 105±2 °C, 96h	①Contact resistance: 30 mΩ MAX. ②Insulation resistance: 1,000MΩ MIN. ③No damage, crack or looseness of parts.	O	—
Cold	Exposed at -55±3 °C, 96h	①Contact resistance: 30 mΩ MAX. ②Insulation resistance: 1,000MΩ MIN. ③No damage, crack or looseness of parts.	O	—
Resistance To Soldering Heat	①Automatic soldering (flow) Soldered at solder temperature, 260 °C for in immersion , duration, 5 s. ②Manual soldering Soldering iron temperature :270 °C, Soldering time :3s. No strength on contact.	No deformation of case of excessive looseness of the terminals.	O	—
Solderability	Soldering temperature: 245 °C Duration of immersion :soldering, for 5 sec.	New uniform coating of solder shall cover minimum of 95 % of the surface Being immersed.	O	—

NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST				
HIROSE KOREA CO.,LTD.		SPECIFICATION SHEET		PART NO. DF51K-16DP-2DS(800)
CODE NO.(OLD) CL	DRAWING NO. ELC4-632482	CODE NO.	CL 6652-0052-2-800	2/2