

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO + 85°C (NOTE1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C	
	OPERATING HUMIDITY RANGE	40 % TO 80 % (NOTE2)	STORAGE HUMIDITY RANGE	40 % TO 70 % (NOTE3)	
	VOLTAGE	250V AC	APPLICABLE CONNECTOR	DF1-*P-2. 5DS (A) (#)	
	CURRENT	AWG 24 : 3 A AWG 26 : 2 A AWG 28 : 1 A	APPLICABLE CONTACT	DF1-2428SC (F)	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ELECTRIC CHARACTERISTICS					
INSULATION RESISTANCE	500V DC.	1000MΩ MIN.	X	-	
VOLTAGE PROOF	650V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	-	
MECHANICAL CHARACTERISTICS					
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2h, FOR EACH, FOR 3 DIRECTIONS.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 1000MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→15 TO 35→85→15 TO 35°C TIME 30→2 TO 3 →30→2 TO 3 min UNDER 5 CYCLES.	① INSULATION RESISTANCE: 1000MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
REMARKS					
NOTE 1: INCLUDING THE TEMPERATURE RISE BY CURRENT.					
NOTE 2: NON-CONDENSING					
NOTE 3: APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD. AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION					
Unless otherwise specified, refer to JIS C 5402.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
			APPROVED	KI. AKIYAMA	10. 05. 11
			CHECKED	HK. UMEHARA	10. 05. 11
			DESIGNED	HT. SATO	10. 05. 11
			DRAWN	MI. SAKIMURA	10. 05. 11
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELG4-162414-01
HRS	SPECIFICATION SHEET		PART NO.	DF1-*S-2. 5C	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL541-	△ 1/1