Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C(NOTE3)
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTE2)	STORAGE HUMIDITY RANGE	20% TO 70%(NOTE3)
	VOLTAGE	150 V AC	CURRENT	1 A
	APPLICABLE CONNECTOR	DF13(A)-20DP-1.25V(##)	APPLICABLE CRIMP CONTACT	DF13(G)-2630SCF(A) DF13(G)-3032SCF(A)

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	100 V DC.	500 MΩ MIN.	X	—
VOLTAGE PROOF	500 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS				
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK	490 m/s^2 DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE –55 →5 TO 35 →+85→5 TO35°C TIME 30 →10 TO 15 →30 →10 TO 15min UNDER 5 CYCLES.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—

REMARKS
NOTE1: INCLUDING THE TEMPERATURE RISE BY CURRENT.
NOTE2:NO CONDENSING
NOTE3:APPLY TO THE CONDITION OF LONGTERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.

Unless otherwise specified, refer to JIS C 5402.

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△0					

APPROVED	TS. SAKATA	08. 12. 10
CHECKED	TS. KUMAZAWA	08. 12. 10
DESIGNED	SN. KOBAYASHI	08. 12. 04
DRAWN	SN. KOBAYASHI	08. 12. 04

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-160104-01

HRS	SPECIFICATION SHEET	PART NO.	DF13-20DS-1.25C	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL536-0555-6-00 △0	1/1

FORM HD0011-2-1