

Nov.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85°C (NOTE1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60°C (NOTE3)	
	OPERATING HUMIDITY RANGE	20% TO 80% (NOTE2)	STORAGE HUMIDITY RANGE	40% TO 70% (NOTE3)	
	VOLTAGE	150 V AC/DC	APPLICABLE CONTACT	DF13-*S-1.25C	
	CURRENT	1 A	APPLICABLE CABLE	AWG26 TO AWG 30	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	20 mV MAX, 1 mA(DC OR 1000 Hz).	30 mΩMAX.	X	-	
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES	<input type="checkbox"/> 0.35±0.002 mm BY STEEL GAUGE.	INSERTION FORCE 3 N MAX. EXTRACTION FORCE 0.3 N MIN.	X	-	
MECHANICAL OPERATION	30 TIMES INSERTION AND EXTRACTION.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2h, FOR 3 DIRECTION.	① NO ELECTRICAL DISCONTINUITY OF 1 μ s. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		X	-	
CRIMP TENSILE STRENGTH		① #AWG26 : 20 N MIN. ② #AWG28 : 10 N MIN. ③ #AWG30 : 5.9N MIN.	X	-	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT(STEADY STATE)	EXPOSED AT 40 ± 2°C , 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→-5 TO 35→+85→-5 TO35 °C TIME 30 →10 TO 15 →30 →10 TO 15min UNDER 5 CYCLES.		X	-	
NOTE 1: INCLUDE THE TEMPERATURE RISING BY CURRENT. NOTE2:NO CONDENSING NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFOR PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITTY RANGE IS APPLIED FOR INTERIM STRAGE DURING TRANSPORTATION.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARKS			APPROVED	HK. UMEHARA	11. 11. 17
			CHECKED	HK. UMEHARA	11. 11. 17
			DESIGNED	HT. SATO	11. 11. 17
Unless otherwise specified, refer to JIS C 5402.			DRAWN	HT. SATO	11. 11. 17
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-162517-01
	SPECIFICATION SHEET		PART NO.	DF13G-2630SCF	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL536-0643-1-00	1/1