

TO

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-30°C TO +85 °C(NOTE1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C(NOTE2)
	VOLTAGE	250 V AC	CURRENT	3 A

SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT

CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	30 mΩ MAX.	X	—
INSULATION RESISTANCE	500 V DC.	1000MΩ MIN.	X	—
VOLTAGE PROOF	650V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—

MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs.	X	—
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—

ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5~35 →+85→ 5~35 °C TIME 30→10~15→ 30 →10~15 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, 250±5°C, FOR. IMMERSION, DURATION, 10 s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 230±5 °C FOR INSERTION DURATION, 5 s.	SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	X	—

REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT. NOTE2:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD,OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION. Unless otherwise specified, refer to JIS C 5402.	M.Nakamoto '04.04.16	H.Umehara '04.04.16	T.Ono 04.04.16	T.Ono 04.04.16	

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

HS	HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET	PART NO.
			DF1-*P-2. 5DSA (05)
CODE NO.(OLD)	DRAWING NO.	PART NO.	
CL	ELC4-162342-10	CL541	1/1