





APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO +85 °C(NOTE1)		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C(NOTE2)	
	VOLTAGE	250 V AC		APPLICABLE CONNECTORS	DF1- * P-2.5DS,DF1- * P-2.5DSA	
	CURRENT	AWG26	 2A	OPERATING HUMIDITY RANGE	UL1007,AWG26	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		30 mΩ MAX.	X	—
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.	X	—
VOLTAGE PROOF		650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS. ① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.			X	—
SHOCK		490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			X	—
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 5 TO 35→85→ 5 TO 35°C TIME 30→ 10 → 30→ 10 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE:1000 MΩMIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.			X	—
REMARKS						
NOTE1:INCLUDING THE TEMPERATURE RISING BY CURRENT. NOTE2:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD AFTER PCBBOARD , OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERM STORAGE DURING TRANSPORTATION.						
Unless otherwise specified, refer to JIS C 5402.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	1	DIS-H-000869	AK.MIURA	HK.UMEHARA	06.03.31	
				APPROVED	TY.OMA	05.12.28
				CHECKED	HK.UMEHARA	05.12.28
				DESIGNED	NS.HIROSE	05.12.27
				DRAWN	AK.MIURA	05.12.27
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-162344-01	
	SPECIFICATION SHEET		PART NO.	DF1-*S-2. 5R26 (05)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL541		1/1