




NOTES 1: IF THERE IS PATTERN ON  PART, THERE IS A POSSIBILITY THAT IT WILL MAKE CONTACT WITH THE LEADS.

2 : LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.


3: RECOMMENDED METAL MASK THICKNESS: 0.15-0.2mm
OPEN AREA RETO: 100%

OPEN AREA RETIO:100%				7	PS	REEL
				6	POLYESTER	CLEAR(COVER TAPE)
2	BRASS	SURFACE:TIN PLATED 1 μ m min UNDER PLATING:NICKEL PLATED 0.5 μ m min		5	PS	CLEAR(EMBOSSSED CARRIER TAPE)
				4	POLYAMIDE	CAP. BLACK
1	POLYAMIDE	BEIGE, UL94V-0		3	BRASS	TIN PLATED 1 μ m min
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS


UNITS mm		SCALE 5 : 1	COUNT 3	DESCRIPTION OF REVISIONS DIS-H-00019792	DESIGNED KI. SUGAWARA	CHECKED SZ. ONO	DATE 20240111
 HIROSE ELECTRIC CO., LTD.		APPROVED :TY. OMA	20050811	DRAWING NO. EDC-306017-27-04			
		CHECED :HK. UMEHARA	20050811	PART NO. DF11Z-*DP-2V(27)			
		DESIGNED :IO. DENPOUYA	20050811	CODE NO. CL543-			
		DRAWN :MK. MATSUO	20050803				

CODE No.	NUMBER OF CONTACT	E	F	G	H	J
DF 11Z- 4DP-2V(27)	4	24.0	—	11.5	13.2	24.4
DF 11Z- 6DP-2V(27)	6	24.0	—	11.5	15.2	24.4
DF 11Z- 8DP-2V(27)	8	24.0	—	11.5	17.2	24.4
DF 11Z-10DP-2V(27)	10	32.0	28.4	14.2	19.2	32.4
DF 11Z-12DP-2V(27)	12	32.0	28.4	14.2	21.2	32.4
DF 11Z-14DP-2V(27)	14	44.0	40.4	20.2	23.2	44.4
DF 11Z-16DP-2V(27)	16	44.0	40.4	20.2	25.2	44.4
DF 11Z-18DP-2V(27)	18	44.0	40.4	20.2	27.2	44.4
DF 11Z-20DP-2V(27)	20	44.0	40.4	20.2	29.2	44.4
DF 11Z-22DP-2V(27)	22	44.0	40.4	20.2	31.2	44.4
DF 11Z-24DP-2V(27)	24	56.0	52.4	26.2	33.2	56.4
DF 11Z-26DP-2V(27)	26	56.0	52.4	26.2	35.2	56.4
DF 11Z-28DP-2V(27)	28	56.0	52.4	26.2	37.2	56.4
DF 11Z-30DP-2V(27)	30	56.0	52.4	26.2	39.2	56.4
DF 11Z-32DP-2V(27)	32	56.0	52.4	26.2	41.2	56.4
DF 11Z-40DP-2V(27)	40	72.0	68.4	34.2	49.2	72.4

STYLE AND DIMENSION OF REEL



DETAIL OF NOTE LABEL



HRG

DRAWING NO.	EDC-306017-27-04
PART NO.	DF11Z-*DP-2V(27)
CODE	C1543-

$\triangle$	2
3	

NOTES 4 : 1 REEL:500 CONNECTORS.

5 : AT THE BEGINNING OF THE REEL, 15 COMPONENTS SHALL BE EMPTY.
AT THE END OF THE REEL, 10 COMPONENTS SHALL BE EMPTY.

6 : WHEN THE TAPE WIDTH IS 32, 44, 56 OR 72mm, SPROCKET HOLES SHALL BE
SET ON BOTH SIDES OF REEL AS SHOWN ON THIS DRAWING.

7 : THE REEL IS WRAPPED IN ALUMINIUM BAG WITH A DRY AGENT INSIDE FOR
MOISTURE-PROOF PACKAGING.

8 : FOR THE STORAGE OF 168 HOURS OR MORE AFTER OPENING THE PACKAGE,
KEEP THE PRODUCTS UNDER MOISTURE PROOF CONDITIONS.

9 : EXCEPT ON THE MATING SURFACE, COMPONENT INFLATION DOES NOT
AFFECT THE PRODUCTS PERFORMANCE.

FORM HC0011-5-8 1

2

3

4

□

8

—

8