Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					

APPLICABLE STANDARD

RATING	OPERATING TEMPERATURE RANGE	-35 °C TO 85 °C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO 60 °C
	VOLTAGE	250 V AC	APPLICABLE CONNECTORS	DF1B-＊DS-2.5R
	CURRENT	3 A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS				
INSULATION RESISTANCE	500 V DC.	1000 MΩ MIN.	×	—
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASH OVER OR BREAKDOWN.	×	—
MECHANICAL CHARACTERISTICS				
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75mm, — m/s^2 AT 2 h, FOR 3 DIRECTIONS.	①NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—
SHOCK	490 m/s^2 DIRECTIONS OF PULSE 11 ms AT 3 TIME FOR 3 DIRECTION.		×	—
ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 →5 TO 35→ 85 →5 TO 35 °C TIME 30 → 5 MAX → 30 →5 MAX min UNDER 5 CYCLES.	① INSULATION RESISTANCE:1000MΩ MIN. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 500 MΩ MIN ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS..	×	—

REMARKS
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT

Unless otherwise specified, refer to MIL-STD-1344.

DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
M.Kuramochi '03.07.16	T.Kumagai '03.07.17	T.Miyazaki '03.07.17	T.Miyazaki '03.07.17	

Note QT: Qualification Test AT: Assurance Test ×:Applicable Test

HRS HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET	PART NO. DF1BA-＊DEP-2.5RC
CODE NO.(OLD) CL	DRAWING NO. ELC4—160043-01	PEART NO CL541

1/1

FORM No.231-1

TO