Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C(NOTE 3)	
	OPERATING HUMIDITY RANGE	40% TO 80%(NOTE 2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTE 3)	
	VOLTAGE	250 V AC	APPLICABLE CONNECTORS	DF1E-※S-2.5C	
	CURRENT	AWG20 - 24 : 3 A AWG26 : 2 A AWG28 : 1 A AWG30 : 0.5 A	UL,CSA	VOLTAGE	AC 30V
				CURRENT	AWG20 - 22 : 3A AWG24 - 28 : 1A AWG30 : 0.5A

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
INSULATION RESISTANCE	500 V DC.	1000 MΩ MIN.	X	—
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS				
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK	490 m/s^2 DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 500 MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE –55→15 TO 35→85→15 TO 35°C TIME 30 → 5MAX →30→ 5MAX min UNDER 5 CYCLES.	① INSULATION RESISTANCE:1000 MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—

REMARKS

NOTE1:INCLUDING THE TEMPERATURE RISING BY CURRENT.
NOTE2:NO CONDENSING.
NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD AFTER PCBBOARD , OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERM STORAGE DURING TRANSPORTATION.

Unless otherwise specified, refer to JIS C 5402.

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
⚠0					

APPROVED	KI. AKIYAMA	10. 06. 29
CHECKED	HK. UMEHARA	10. 06. 29
DESIGNED	HT. SATO	10. 06. 29
DRAWN	MI. SAKIMURA	10. 06. 22

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-161950-01

HRS

SPECIFICATION SHEET — PART NO. DF1EA-*EP-2.5C

HIROSE ELECTRIC CO., LTD. — CODE NO. CL541 — ⚠0 — 1/1

FORM HD0011-2-1