




PROPERTY SURVEY FORM FOR SALES WITH NO INTERESTS						
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS
1	RE-F-09671	K.N	H.Y	04.04.08		
2	RE-F-10252	K.D	H.O	04.12.06		
				.		
				.		
				.		



RECOMMENDED LAND PATTERN DIMENSION OF P.C.B. (MOUNTING SIDE)



DIMENSION TABLE OF CONNECTOR AND P.C.B. LAND PATTERN.

PART No.	CODE No.		6	7	A	B	C	D	E
FX8C- 60P-SV(93)	Cl.578-0501-9-93	60	×	×	24.60	23.00	20.70	17.40	22.20
FX8C- 80P-SV(93)	Cl.578-0503-4-93	80	×	×	30.60	29.00	26.70	23.40	28.20
FX8C-100P-SV(93)	Cl.578-0505-0-93	100	×	×	36.60	35.00	32.70	29.40	34.20
FX8C-120P-SV(93)	Cl.578-0506-2-93	120	—	—	42.60	41.00	38.70	35.40	40.20
FX8C-140P-SV(93)	Cl.578-0507-5-93	140	—	—	48.60	47.00	44.70	41.40	46.20

NOTE 1. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.

2. EMBOSSED CARRIER TAPE PACKAGING SHALL BE APPLIED TO THIS PRODUCT.

SEE NEXT PAGE FOR DETAILS.

3. THIS PRODUCT HAS TAPE FOR VACUUM PICKUP.

SEE NEXT PAGE FOR DETAIL OF STICKING POSITION, ETC.

4. FOR MODIFICATION, ETC. PREVENTIVE HOLE FOR SINK MARK MAY BE ADDED ACCORDING TO CIRCUMSTANCES.

5. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

6 NUMBER OF CONTACTS:

7

X: PRODUCED. -: NO PRODUCED.

1	POLYPHENYLENE SULFIDE	LIGHT BROWN (UL94V-0)	2	PHOSPHOR BRONZE	CONTACT AREA: GOLD 0.1 μm min
					LEAD AREA: GOLD FLASH
					UNDER PLATING: NICKEL 0.5 μm min
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	S. SUZUKI	K. NAKAMURA	H. OKAWA	Y. YOSHIMURA	
	03.02.03	03.02.12	03.02.14	03.02.15	

	DRAWING NO.		PART NO.	FX8C-**-P-SV(93)
	SCALE	EDC3-151020-23		
	FREE		CODE NO.	CL578
	UNITS	HIROSE ELECTRIC CO., LTD		
		mm	1/2	

TO	PCK			
----	-----	--	--	--

