

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-30°C TO 85°C (NOTE 1)		STORAGE TEMPERATURE RANGE	-10°C TO 60°C (NOTE 2)
	OPERATING HUMIDITY RANGE	40% TO 80%		STORAGE HUMIDITY RANGE	40% TO 70% (NOTE 2)
	VOLTAGE	AC 250V		VOLTAGE	AC 30V
	CURRENT	AWG 22 TO 26 : 2A AWG 28 : 1A AWG 30 : 0.5A		UL • CSA RATING CURRENT	AWG 22 : 2A AWG 24 TO 28 : 1A AWG 30 : 0.5A
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	
MARKING		CONFIRMED VISUALLY.			
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		30 mΩ MAX.	
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.	
VOLTAGE PROOF		650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTATIONS.		① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
SHOCK		490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 5 TO 35→+85→ 5 TO 35 °C TIME 30→ 5 TO 15→ 30→ 5 TO 15 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 1000MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 500MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	
RESISTANCE TO SOLDERING HEAT		1) AUTOMATIC SOLDERING (REFLOW) 《REFLOW AREA》 MAX 240°C WITHIN 10 sec. MIN 220°C WITHIN 30sec. 《PREHEATING AREA》 150°C 100 TO 120 sec. PUT THROUGH IN REFLOW FURNACE TWICE. FEAVE IN AMBIENT TEMPERATURE AND HUMIDITY FOR 1 HOUR. CONNEVCTOR TEMPERATURE TO BE AMBIENT FOR SECOND REFLOW. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE :290±10°C, SOLDERING TIME :3s. NO STRENGTH ON CONTACT.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 230±5°C FOR IN IMMERSION , DURATION, 3 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARKS			APPROVED	TS. SAKATA	08.12.16
NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT.			CHECKED	TS. KUMAZAWA	08.12.15
NOTE 2:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD , AFTER PCB BOARD , OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERM STORAGE DURING TRANSPORTATION.			DESIGNED	KT. ISHII	08.12.15
Unless otherwise specifid , refer to JIS C 5402.			DRAWN	KT. ISHII	08.12.15
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-162226-01
	SPECIFICATION SHEET		PART NO.	DF11G-26DP-2V (50)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL543-0821-6-50	1/1