


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



CROSS CUT SECTION (10:1)



RECOMMENDED LAND PATTERN DIMENSION OF PCB
(RECOMMENDED METAL MASK THICKNESS:0.15mm)



HRS DRAWING FOR REFERENCE

STACKING HEIGHT

	FX10A-168S-SV(83)	
	4 (A)	5 B
FX10A(B)-168P-SV(**)	4	4.3±0.127
FX10A(B)-168P-SV1(**)	5	5.3±0.127
FX10A(B)-168P-SV2(**)	6	6.0±0.127
FX10A(B)-168P-SV3(**)	7	7.0±0.127
FX10A(B)-168P-SV4(**)	8	8.0±0.127

NOTES
1. SMT LEAD-COPLANARITY:0.1 MAX.
2. THIS PRODUCT HAS NO POLARITY TO PATTERN FOR MOUNTING.
3. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
4. STACKING HEIGHT FROM LEAD TO LEAD(REFERENCE DIMENSIONS)
5. BOARD DISTANCE
6. ▨ AREA IS VACUUM PICKUP AREA FOR REFERENCE.

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
2	PHOSPHOR BRONZE	CONTACT AREA:GOLD 0.76μm min. LEAD AREA:GOLD 0.03μm min. UNDER PLATING:NICKEL 1.3μm min.	4	PS	
1	LCP	BEIGE UL94V-0	3	PHOSPHOR BRONZE	SURFACE AREA:GOLD 0.03μm min. UNDER PLATING:NICKEL 1.3μm min.


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	4 : 1	△					

HIROSE ELECTRIC CO., LTD.


APPROVED	HS. OKAWA	12.11.16	DRAWING NO. EDC3-151987-02
CHECKED	HT. YAMAGUCHI	12.11.16	PART NO. FX10A-168S-SV(93)
DESIGNED	YJ. ASAO	12.11.15	CODE NO. CL570-0244-7-93
DRAWN	YJ. ASAO	12.11.15	△ 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DRAWING FOR PACKING(2:1)



A(1:1)



HRS DRAWING FOR REFERENCE

NOTES 1 1TRAY:50 CONNECTORS.
2 THIS PRODUCT HAS NO POLARITY TO TRAY PACKAGING.
3 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

HRS	図番：	EDC3-151987-02
	製品名：	FX10A-168S-SV(93)
	製品コード	CL570-0244-7-93 △ 2/2