

APPLICABLE STANDARD						
RATING	Operating Temperature Range	-55°C to 85°C (Note 1)	Storage Temperature Range	-10°C TO 60°C		
	Voltage	30V AC/DC				
	Current	Signal contact : 0.3A				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
General Examination		Visually and by measuring instrument.		According to drawing.	X	X
Marking		Confirmed visually.		According to drawing.	X	X
ELECTRIC CHARACTERISTICS						
Contact Resistance		20mV AC or less 1kHz,1m A .		Signal contact resistance: 100 mΩ MAX.	X	—
Insulation Resistance		100V DC.		100 MΩ MIN.	X	—
Voltage Proof		150V AC for 1 min.		No flashover or breakdown.	X	—
Voltage Standing Wave Ratio	Frequency 0 ~ 3 GHz		VSWR 1.3 Max.		X	—
	Frequency 3 ~ 6 GHz		VSWR 1.4 Max.			
	Frequency 6 ~ 12 GHz		VSWR 1.6 Max			
MECHANICAL CHARACTERISTICS						
Mechanical Operation		10times insertions and extractions.		① Signal contact resistance: 100 mΩ MAX. ② No damage, crack or looseness of parts.	X	—
Vibration		Frequency 10 to 55 to 10 Hz, approx 5min, Single amplitude 0.75 mm,10cycles, for 3 directions.		① No electrical discontinuity of 1 μs. ② No damage, crack or Looseness of parts.	X	—
Shock		490 m/s <sup>2</sup> duration of pulse 11 ms at 3 times for 3 directions.		① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.	X	—
Insertion and Withdrawal forces		Measured by applicable connector. 30times insertions and withdrawal. Test speed 10mm/min.		① Insertion forces: 30N MAX. ② Withdrawal forces: 4N MIN.	X	—
ENVIRONMENTAL CHARACTERISTICS						
Rapid Change of Temperature		Temperature -55 → +85°C Time 30 → 30 min Under 5 cycles. (Relocation time to chamber : within 2-3 min)		① Signal contact resistance: 100 mΩ MAX. ② Insulation resistance: 100MΩ MIN. ③ No damage, crack or looseness of parts.	X	—
Damp Heat (Steady state)		Exposed at 40 ± 2 °C, 90 to 95 %, 96 h.		① Signal contact resistance: 100 mΩ MAX. ② Insulation resistance: 50MΩ MIN. ③ No damage, crack or looseness of parts.	X	—
Sulfur Dioxide		Exposed in 25 PPM for 96h, 25°C, 75%. (Refer to IEC 60068-2-42 Test Kc)		Signal contact resistance: 100 mΩ MAX.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
⚠						
REMARKS			APPROVED	WR. FUKUCHI	18. 07. 21	
Note1: Include the temperature rising by current			CHECKED	TY. 001	18. 07. 21	
Unless otherwise specified, refer to IEC 60512.			DESIGNED	RH. KITAGAWA	18. 07. 21	
			DRAWN	SN. NUMAZAKI	18. 07. 21	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-378955-51-03	
HRS	SPECIFICATION SHEET		PART NO.	BM46B-12DS-0. 35V (51)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL673-7054-0-51	⚠	1/1