

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD			
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTE1)	STORAGE TEMPERATURE RANGE
	VOLTAGE	500V AC	APPLICABLE CONNECTOR
	CURRENT	AWG18 MAX 8A AWG20 MAX 6A AWG22 MAX 5A	APPLICABLE CABLE

SPECIFICATIONS						
ITEM	TEST METHOD	REQUIREMENTS	QT AT			
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	○ ○			
MARKING	CONFIRMED VISUALLY.		○ ○			
ELECTRICAL CHARACTERISTICS						
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	30 mΩ MAX.	○ —			
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV MAX, Ma(DC OR 1000 Hz).	mΩ MAX.	— —			
INSULATION RESISTANCE	500V DC.	1000 MΩ MIN.	○ —			
VOLTAGE PROOF	1500V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	○ —			
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES	□ 1.14 ± 0.002 BY STEEL GAUGE.	INSERTION FORCE 4.5 N MAX. EXTRACTION FORCE 0.3 N MIN.	○ —			
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE N MAX. EXTRACTION FORCE N MIN.	— —			
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	○ —			
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, - m/s ² AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10μs.	○ —			
SHOCK	490m/s ² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.	② CONTACT RESISTANCE: 30mΩ MAX. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	○ —			
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 15~35→ +85→15~35°C TIME 30→ 10~15→ 30→10~15 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30mΩ MAX. ② INSULATION RESISTANCE: 1000MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	○ —			
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2°C, 90~95%, 96h.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	○ —			
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, °C, FOR IMMERSION, DURATION, s.	NO DEFORMATION ON CASE OR EXCESSIVE LOOSENESS OF THE TERMINALS.	— —			
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, °C FOR IN IMMERSION, DURATION, s.	SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	— —			
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT.		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
Unless otherwise specified, refer to MIL-STD-1344.		<i>Miyazaki</i>	<i>Miyazaki</i>	<i>C. Hanami</i>	<i>K. Katayama</i>	
		99.1.27	99.1.27	99.1.30	99.2.1	
Note QT:Qualification Test AT:Assurance Test ○:Applicable Test						
HS HIROSE ELECTRIC CO., LTD.		SPECIFICATION SHEET		PART NO.		
CODE NO.(OLD)		DRAWING NO.		CODE NO.		
CL		ELC4-160130		CL 676-0002-4		

TO