




- NOTE 1. ALL LEADS CO-PLANARITY SHALL BE 0.1 mm MAX.
2. PER REEL : 1000 CONNECTORS.
3. AT THE BEGINNING OF THE REEL, 100 mm AT MIN SHALL BE EMPTY POCKETS.
AT THE END OF THE REEL, 160 mm AT MIN SHALL BE EMPTY.
4. CONTACT PLATING SPECIFICATIONS.
CONTACT AREA : GOLD 0.1μm MIN.
SMT LEAD : GOLD 0.05μm MIN.
UNDERPLATING : NICKEL 1μm MIN.
(SURFACE : SEALING)
5. METAL HOLD DOWN PLATING SPECIFICATIONS.
MOUNTING AREA: GOLD 0.05μm MIN.
UNDERPLATING : NICKEL 1μm MIN.
6. PEEL FORCE OF COVER TAPE REFERS TO JIS C 0806.

RECOMMENDED METAL MASK OPENING PATTERN






RECOMMENDED SOLDER PASTE THICKNESS: 120μm

RECOMMENDED PATTERN



ENGAGEMENT FIGURE



3	PHOSPHOR BRONZE	5	6	PS	PLASTIC REEL (BLACK)					
2	PHOSPHOR BRONZE	4	5	POLYESTER	CLEAR(COVER TAPE)					
1	LCP	UL94V-0, BLACK	4	PS	CLEAR(EMBOSSED CARRIER TAPE)					
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS				
UNITS mm			SCALE FREE		COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
HRS HIROSE ELECTRIC CO., LTD.		APPROVED : KH. IKEDA		09.02.06		DRAWING NO.		EDC3-308583-04		
		CHECED : TS. MIYAZAKI		09.02.06		PART NO.		DF37B-20DP-0.4V(74)		
		DESIGNED : RT. SHIMIZU		09.02.06		CODE NO.		CL684-3008-1-74		
		DRAWN : AK. AOYAGI		09.02.06						
								1/2		

