



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.








A-A (50:1)



HRS DRAWING FOR REFERENCE

NOTE 1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX
2. CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD 0.05μm MIN
SMT LEAD : GOLD 0.05μm MIN
UNDER PLATING : NICKEL 1μm MIN
(SURFACE : SEALING)
3. EACH CONTACTS AT 4 CORNERS ARE PROVIDED FOR METAL FITTINGS.
4. HRS MARK AND CAV No. ARE INDICATED IN APPROX POSITION SHOWN.
5. A PART OF THE WALL COULD BE NOTCHED.

ENGAGEMENT FIGURE (50:1)



NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	PS	CLEAR (EMBOSSED CARRIER TAPE)	6	PS	CLEAR (REINFORCEMENT COLLAR)
2	PHOSPHOR BRONZE	2	5	PS	BLACK (PLASTIC REEL)
1	LCP	UL94 V-0, BLACK	4	POLYESTER	CLEAR (COVER TAPE)


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	10 : 1	3	1	DIS-H-008208	KR. AJITO	TS. MIYAZAKI	13.10.09

HIROSE ELECTRIC CO., LTD.

APPROVED	KH. IKEDA	12.11.19	DRAWING NO. EDC3-347090-01
CHECKED	WR. FUKUCHI	12.11.19	PART NO. BM20B(0.6)-30DP-0.4V(51)
DESIGNED	RT. SHIMIZU	12.11.19	
DRAWN	YS. YAMAZAKI	12.11.17	CODE NO. CL684-9303-4-51 3 1/3


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

◈RECOMMENDED PCB LAYOUT




◈RECOMMENDED METAL MASK DIMENSIONS

METAL MASK THICKNESS : 100μm



6 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.



REFLOW METHOD:IR REFLOW
NUMBER OF REFLOW CYCLES:2 CYCLES MAX.
1)REFLOW TIME
  DURATION ABOVE 220℃, 60 SEC MAX.
  (PEAK TEMPERATURE:250℃ MAX)
2)PRE-HEAT TIME
  PRE-HEAT TEMPERATURE(MIN):150℃
  PRE-HEAT TEMPERATURE(MAX):180℃
  PRE-HEAT TIME:90-120 SEC.


6 THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDISIONAL FACTORS. SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.


HRS DRAWING FOR REFERENCE

HRS	DRAWING NO.	EDC3-347090-01
	PART NO.	BM20B(0.6)-30DP-0.4V(51)
	CODE NO.	CL684-9303-4-51


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


EMBOSSED CARRIER TAPE PACKAGING (5:1)













9 TAPING(FREE)

STYLE AND DIMENTION OF REEL (FREE)



L-L (FREE)



DETAIL OF PART No. LABEL

製造年月日	** ** **	DATE OF MANUFACTURED
製品コード	CL684-9303-4-51	CODE No.
製品名	BM20B(0.6)-30DP-0.4V(51)	PART No.
数量	8,000	QUANTITY
納入者	ヒロセ電機(株)	SUPPLIER

7. PER REEL 8000 CONNECTORS.
8. THE DIMENTIONS IN PARENTHESES ARE FOR REFFERENCE.
9. REFER TO JIS C 0806(PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLIMG)
10. AFTER PACKAGING, ROLL 2 METERS OF THE REINFORCEMENT COLLAR TO OUTER CIRCUMFERENCE OF TAPE AND REEL POCKET. AND TAPE DOWN AT THE END THE COLLAR.

HRS DRAWING FOR REFERENCE

HRS	DRAWING NO.	EDC3-347090-01
	PART NO.	BM20B(0.6)-30DP-0.4V(51)
	CODE NO.	CL684-9303-4-51
		3 / 3