



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.






- NOTE 1. The procedure of cable assemblies would be confirm to the ETAD-K0189.
2. When this plug is mated with a MF10S receptacle, the clamp torque of the part No. ② should be 1.5 to 3 N·m. Following MF10-T1 can be used as simple substitution of a torque wrench.

EXCLUSIVE PLASTIC SPANNER	PART NO.	CODE NO.
	MF10-T1	CL709-0205-8

③ The ferrule parts are not contained. Please use the 'MU simplex simplified plug' chosen from the Table 1 according to the outer diameter of the optical fiber.

Table 1. MU simplex simplified plug (without hood) ③

Part No.	HRS CL No.	Ferrele Inner dia.
HMUA-FK-A125(C01)	CL710-0099-2-01	φ 0.125 ^{+0.001} ₀
HMUA-FK-A1255(C01)	CL710-0107-9-01	φ 0.1255 ^{+0.001} ₀
HMUA-FK-A126(C01)	CL710-0100-0-01	φ 0.126 ^{+0.001} ₀

7	BRASS	CHROME PLATING	14	ZIRCONIA	
6	SYNTHETIC RUBBER		13	STAINLESS STEEL	
5	SYNTHETIC RUBBER		12	STAINLESS STEEL	NYELOCK
4	SYNTHETIC RESIN		11	ALUMINIUM ALLOY	ANODIC OXIDE COATING
3	ALUMINIUM ALLOY	ANODIC OXIDE COATING	10	STAINLESS STEEL	
2	BRASS	CHROME PLATING	9	SYNTHETIC RESIN	
1	ZINC DIECAST	CHROME PLATING	8	SYNTHETIC RUBBER	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
		APPROVED : MT. SHIBUTANI 18. 03. 16		DRAWING NO. EDC-175688-31-00	
HIROSE ELECTRIC CO., LTD.		CHECKED : FS. YOSHIDA 18. 03. 16		PART NO. MF10S-WP7C01-0200(31)	
		DESIGNED : SI. MATSUMOTO 18. 03. 15		CODE NO. CL709-0203-2-31	
		DRAWN : SR. TOYOKAWA 18. 03. 15		