

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	$\triangle$ -55℃ TO 85℃ (NOTE 1)	STORAGE TEMPERATURE RANGE	-10℃ TO 60℃		
	VOLTAGE	$\triangle$ 50V AC/DC	APPLICABLE CONNECTOR	BM28B0. 6-34DP/2-0. 35V		
	CURRENT	SIGNAL CONTACT : 0. 3A MAX (TOTAL CONTACTS 10A MAX) $\triangle$ POWER CONTACT : 5. 0A				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		20mV AC OR LESS 1kHz,1m A .		Signal contact resistance: 70 mΩ MAX. $\triangle$ Power contact resistance: 15 mΩ MAX. $\triangle$	X	-
INSULATION RESISTANCE		100V DC.		50MΩ MIN.	X	-
VOLTAGE PROOF		150V AC FOR 1 min. $\triangle$		NO FLASHOVER OR BREAKDOWN.	X	-
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		10TIMES INSERTIONS AND EXTRACTIONS.		① Signal contact resistance: 70 mΩ MAX. $\triangle$ Power contact resistance: 15 mΩ MAX. $\triangle$ ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz,APPROX 5min, SINGLE AMPLITUDE 0.75 mm,10CYCLES, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHANBER : WITHIN 2-3 min)		① Signal contact resistance: 70 mΩ MAX. $\triangle$ Power contact resistance: 15 mΩ MAX. $\triangle$ ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① Signal contact resistance: 70 mΩ MAX. $\triangle$ Power contact resistance: 15 mΩ MAX. $\triangle$ ② INSULATION RESISTANCE: 25MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h,25℃,75%. (REFER TO JIS C 60068)		① Signal contact resistance: 70 mΩ MAX. $\triangle$ Power contact resistance: 15 mΩ MAX. $\triangle$	X	-
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
$\triangle$	9	DIS-H-00019757	ST. HIRONAKA	RT. SHIMIZU	20240125	
REMARKS			APPROVED	MO. ISHIDA	20170105	
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT			CHECKED	TS. MIYAZAKI	20170105	
Unless otherwise specified, refer to JIS C 5402 and IEC 60512.			DESIGNED	RT. SHIMIZU	20161229	
			DRAWN	RT. SHIMIZU	20161229	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-370835-51-01	
HRS	SPECIFICATION SHEET		PART NO.	BM28B0. 6-34DS/2-0. 35V (51)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0673-5065-0-51	$\triangle$	1/1