







Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT




MATED CONNECTORS



NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM

: IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
90~120s

2. TEMPERATURE FOR SOLDERING IRON
: 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




3	BRASS	SURFACE PLATING : TIN PLATING 1μm min			
		UNDER PLATING : NICKEL 1μm min	6	POLYESTER	
2	BRASS	SURFACE PLATING : TIN PLATING 1μm min	5	POLYSTYRENE	
		UNDER PLATING : NICKEL 1μm min	4	BRASS	SURFACE PLATING : TIN PLATING 1μm min
1	PA	BLACK UL94V-0			UNDER PLATING : NICKEL 1μm min
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 6	DESCRIPTION OF REVISIONS DIS-T-00003979	DESIGNED YONGMUN LEE
HIROSE ELECTRIC CO., LTD.		APPROVED : HK. UMEHARA	20170912	DRAWING NO.	EDC-368630-00-00
		CHECKED : HK. UMEHARA	20170912	PART NO.	ZE05-12DP-2H
		DESIGNED : AH. EDASHIGE	20170911	CODE NO.	CL752-2104-0-00
		DRAWN : MN. SATOH	20170911		


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKING STYLE

PACKING STYLE DRAWING




REEL DIMENSION (FREE)



CARDBOARD DIMENSION (FREE)

W=(405) (mm)
D=(405) (mm)
H=(51) (mm)



HRS	DRAWING NO.	EDC-368630-00-00	2 2
	PART NO.	ZE05-12DP-2H	
	CODE NO.	CL752-2104-0-00	