

| APPLICABLE STANDARD | | | | | | |
|--|-----------------------------|---|---------------------------|--|------------------|-----|
| RATING | Operating Temperature Range | -55°C to 85°C (Note 1) | Storage Temperature Range | -10°C TO 60°C | | |
| | Voltage | 30V AC/DC | | | | |
| | Current | Signal contact : 0.3A | | | | |
| SPECIFICATIONS | | | | | | |
| ITEM | | TEST METHOD | | REQUIREMENTS | QT | AT |
| CONSTRUCTION | | | | | | |
| General Examination | | Visually and by measuring instrument. | | According to drawing. | X | X |
| Marking | | Confirmed visually. | | According to drawing. | X | X |
| ELECTRIC CHARACTERISTICS | | | | | | |
| Contact Resistance | | 20mV AC or less 1kHz,1m A . | | Signal contact resistance: 100 mΩ MAX. | X | — |
| Insulation Resistance | | 100V DC. | | 100 MΩ MIN. | X | — |
| Voltage Proof | | 150V AC for 1 min. | | No flashover or breakdown. | X | — |
| Voltage Standing Wave Ratio | Frequency 0 ~ 3 GHz | | VSWR 1.3 Max. | | X | — |
| | Frequency 3 ~ 6 GHz | | VSWR 1.4 Max. | | | |
| | Frequency 6 ~ 12 GHz | | VSWR 1.6 Max | | | |
| MECHANICAL CHARACTERISTICS | | | | | | |
| Mechanical Operation | | 10times insertions and extractions. | | ① Signal contact resistance: 100 mΩ MAX. ② No damage, crack or looseness of parts. | X | — |
| Vibration | | Frequency 10 to 55 to 10 Hz, approx 5min, Single amplitude 0.75 mm,10cycles, for 3 directions. | | ① No electrical discontinuity of 1 μs. ② No damage, crack or Looseness of parts. | X | — |
| Shock | | 490 m/s ² duration of pulse 11 ms at 3 times for 3 directions. | | ① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts. | X | — |
| Insertion and Withdrawal forces | | Measured by applicable connector. 30times insertions and withdrawal. Test speed 10mm/min. | | ① Insertion forces: 30N MAX. ② Withdrawal forces: 4N MIN. | X | — |
| ENVIRONMENTAL CHARACTERISTICS | | | | | | |
| Rapid Change of Temperature | | Temperature -55 → +85°C Time 30 → 30 min Under 5 cycles. (Relocation time to chamber : within 2-3 min) | | ① Signal contact resistance: 100 mΩ MAX. ② Insulation resistance: 100MΩ MIN. ③ No damage, crack or looseness of parts. | X | — |
| Damp Heat (Steady state) | | Exposed at 40 ± 2 °C, 90 to 95 %, 96 h. | | ① Signal contact resistance: 100 mΩ MAX. ② Insulation resistance: 50MΩ MIN. ③ No damage, crack or looseness of parts. | X | — |
| Sulfur Dioxide | | Exposed in 25 PPM for 96h, 25 °C, 75%. (Refer to IEC 60068-2-42 Test Kc) | | Signal contact resistance: 100 mΩ MAX. | X | — |
| | | | | | | |
| | COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE | |
| ⚠ | | | | | | |
| REMARKS | | | APPROVED | WR. FUKUCHI | 18. 07. 21 | |
| Note1: Include the temperature rising by current | | | CHECKED | TY. 00I | 18. 07. 21 | |
| Unless otherwise specified, refer to IEC 60512. | | | DESIGNED | RH. KITAGAWA | 18. 07. 21 | |
| | | | DRAWN | SN. NUMAZAKI | 18. 07. 21 | |
| Note QT:Qualification Test AT:Assurance Test X:Applicable Test | | | DRAWING NO. | | ELC-378956-51-03 | |
| HRS | SPECIFICATION SHEET | | PART NO. | BM46B-12DP-0. 35V (51) | | |
| | HIROSE ELECTRIC CO., LTD. | | CODE NO. | CL673-7055-0-51 | ⚠ | 1/1 |