

Oct.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO 105 °C (NOTE1)	STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C	
	VOLTAGE	250 V AC	CURRENT	1 A	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	○	○	
MARKING	CONFIRMED VISUALLY.		○	○	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	1A DC.	SIGNAL: 30 mΩ MAX, SHIELD: 60 mΩ MAX.	○	-	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	SIGNAL: 30 mΩ MAX, SHIELD: 60 mΩ MAX.	○	-	
INSULATION RESISTANCE	500 V DC	100 MΩ MIN.	○	-	
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	○	-	
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES	BY STEEL GAUGE, --.	INSERTION FORCE -- N MAX. EXTRACTION FORCE -- N MIN.	-	-	
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① SIGNAL:30mΩ MAX, SHIELD:60mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	-	
VIBRATION	FREQUENCY 20 TO 200 Hz, 43.1 m/s ² AT 3 h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② SIGNAL:30mΩ MAX, SHIELD:60mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	-	
SHOCK	FREQUENCY 20 TO 50 Hz, 66.6 m/s ² AT 1 h.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② SIGNAL:30mΩ MAX, SHIELD:60mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	-	
LOCK STRENGTH	APPLYING A PULL FORCE THE MATING AXIALLY AT 78.4N MAX.	① DURING APPLYING, MATING COMPLETELY. ② AFTER APPLYING, NO DEFECT OF MATING PARTS.	○	-	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.	① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-40→5 TO 35→ 85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	-	
DRY HEAT	EXPOSED AT 105°C, 300 h.	① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX. ② NO HEAVY CORROSION.	○	-	
COLD	EXPOSED AT -55°C, 120 h.	① SIGNAL:60mΩ MAX, SHIELD:120mΩ MAX. ② NO HEAVY CORROSION.	○	-	
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, 260 °C FOR IMMERSION, DURATION, 10s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	-	-	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245 °C FOR IMMERSION DURATION, 3s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	-	-	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARK			APPROVED	KS. SATOH	08.04.01
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.			CHECKED	KS. SATOH	08.04.01
			DESIGNED	TY. IKEDA	08.04.01
			DRAWN	TY. IKEDA	08.04.01
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-166939-00	
HRS	SPECIFICATION SHEET		PART NO.	GT17H-4S-2C (B)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	GL767-0168-4-00	△ 1/1