

May.1.2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +120 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C <sup>(1)</sup>	
	CURRENT	30 A	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX (NOT DEWED)	
	VOLTAGE	600 V AC/DC			
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
<b>CONSTRUCTION</b>					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x	
MARKING	CONFIRMED VISUALLY.		x	x	
<b>ELECTRIC CHARACTERISTICS</b>					
CONTACT RESISTANCE	10A DC.	POWER:3mΩ/SIGNAL:10mΩ /SHIELD:50mΩ MAX.	x	-	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 10mA(DC OR 1000Hz)	POWER:3mΩ/SIGNAL:10mΩ /SHIELD:50mΩ MAX.	x	-	
INSULATION RESISTANCE	1000 V DC.	100 MΩ MIN.	x	-	
VOLTAGE PROOF	2500 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	x	-	
<b>MECHANICAL CHARACTERISTICS</b>					
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: POWER:5mΩMAX/SIGNAL:20mΩMAX ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s <sup>2</sup> ) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7ΩMIN , 1μs MIN. ② CONTACT RESISTANCE: POWER:5mΩMAX/SIGNAL:20mΩMAX ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
LOCK STRENGTH	MEASURE BREAK STRENGTH OF THE LOCK BY PULLING THE CONNECTOR IN THE MATING DIRECTION.	98N MIN.	x	-	
DESTRUCTION TORQUE	WHEN ACTUAL MEASURED PANEL, PLEASE TIGHTEN A SCREW. M4 SCREW BE USED, 2.88N · m(MAX)	WITHOUT DESTRUCTION	x	-	
<b>ENVIRONMENTAL CHARACTERISTICS</b>					
DAMP HEAT (STEADY STATE)	EXPOSED AT 85 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: POWER:5mΩMAX/SIGNAL:20mΩmax ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →120°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: POWER:5 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
DRY HEAT	EXPOSED AT 125°C, 300 h.	① CONTACT RESISTANCE: POWER:5mΩMAX/SIGNAL:20mΩMAX ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
COLD	EXPOSED AT -40°C , 120 h.	① CONTACT RESISTANCE: POWER:5mΩMAX/SIGNAL:20mΩMAX ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
RESISTANCE TO SO <sub>2</sub> GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	CONTACT RESISTANCE: POWER:5mΩMAX/SIGNAL:20mΩMAX	x	-	
WATERPROOFNESS	SINKING TO WATER AFTER EXPOSED AT 125°C WITH CONNECTORS MATED AND ATTACHED TO RECOMMENDED PANEL.	NO WATER IS INSIDE THE CONNECTOR.	x	-	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARK				APPROVED	20180928
(NOTE1) "STORAGE" means a long-term storage state for the unused product.				CHECKED	20180928
				DESIGNED	20180928
				DRAWN	20180926
Note	QT:Qualification Test	AT:Assurance Test	X:Applicable Test	DRAWING NO.	ELC-377226-00-00
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	HVH-280-2/2P-HU (A)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL778-0510-0-00	△ 1/1