

Sep. 1. 2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C (NOTE 3)	
	OPERATING HUMIDITY RANGE	40% TO 80% (NOTE 2)	STORAGE HUMIDITY RANGE	40% TO 70% (NOTE 3)	
	VOLTAGE	500V AC/DC	APPLICABLE CABLE	UL1007, AWG20-22	
	CURRENT	AWG 20 : 5A AWG 22 : 4A	APPLICABLE CONTACT	DF33A-2022SC (F)	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ELECTRIC CHARACTERISTICS					
INSULATION RESISTANCE	500V DC.	1000MΩ MIN.	X	-	
VOLTAGE PROOF	1500V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	-	
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 10 CYCLE FOR EACH, FOR 3 DIRECTIONS.	NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		X	-	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 500MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→+85°C TIME 30→ 30min. UNDER 5 CYCLES. THE TRANSFERRING TIME OF THE TANK IS 2~3 min.	① INSULATION RESISTANCE: 1000MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
REMARKS					
NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT.					
NOTE 2:NO CONDENSING					
NOTE3:APPLY TO THE CONDITION OF LONGTERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
Unless otherwise specifid , refer to JIS C 5402.			APPROVED	KI. AKIYAMA	13. 11. 29
			CHECKED	TS. KUMAZAWA	13. 11. 28
			DESIGNED	HT. SATO	13. 11. 28
			DRAWN	MI. SAKIMURA	13. 11. 27
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-338394-02	
	SPECIFICATION SHEET		PART NO.	DF33C-6DS-3. 3C	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL676-1120-6-00	1/1