

Δ COUNT		REVISIONS		BY	CHKD	DATE	Δ COUNT		REVISIONS		BY	CHKD	DATE
Δ						.	Δ						.
Δ						.	Δ						.

APPLICABLE STANDARD													
RATING	VOLTAGE	CONTACT No. / ~ *	AC 250 V			APPLICABLE CABLES							
	CURRENT	CONTACT No. / ~ *	3 A			IMPEDANCE FREQUENCY RANGE		Ω (0 ~ Hz)					
	POWER					OPERATING TEMPERATURE RANGE		- 35 °C ~ +85 °C (Notes:1)					
	SPECIALTY												

SPECIFICATIONS

No.	ITEM	CONDITIONS	TEST STANDARD	MIN	MAX	UNITS	QT.	AT
1	DESIGN-MATERIAL-FINISH	ADC Applicable std. and dc 3-160092-02		-	-	-	○	○
2	MARKING			-	-	-	○	○
3	INSULATION RESISTANCE	Must be over standard value at DC 500V.	MIL-STD-1344	1000	-	MΩ	○	-
4	CONTACT RESISTANCE	The voltage drop must be under the std. value at DC 0.1 A.	MIL-STD-1344	-	30	mΩ	○	-
	UNIT CONTACT	The voltage drop must be under the std. value at DC A.		-	-	mΩ	-	-
5	DIELECTRIC WITHSTANDING VOLTAGE	Must withstand AC dc 650V for one minute.	MIL-STD-1344	-	-	-	○	-
6	LOW LEVEL CIRCUIT	The Contact Resistance must be under the std. value at DC20mV less and mA.		-	-	mΩ	-	-
7	DRY CIRCUIT	Must have conductivity in alternate current at DC μV.		-	-	-	-	-
8	CONTACT ENGAGEMENT AND SEPARATION FORCES	Must be suitable for the std. gauge size value at applicable gauge.		-	-	gf	-	-
	MATING AND UNMATING FORCES	Must be suitable for the std. value.		-	-	kof	-	-
9	HUMIDITY	Insulation resistance must be over the std. value at - 40±2°C 90 ~ 95 %, 96 hours. at high humidity after high humidity	MIL-STD-1344	1000	-	MΩ	○	-
10	VIBRATION	Must have no damage, crack and looseness of parts at Frequency range 10 ~ 55 Hz, amplitude 0.75mm, -G at 2 hours for 3 directions.	MIL-STD-1344	-	-	-	○	-
11	SHOCK	Must have no damage, crack and looseness of parts after 3 cycles at 490m/s ² in 3 directions.	MIL-STD-1344	-	-	-	○	-
12	TEMPERATURE CYCLING	Must have no damage, crack and looseness of parts for -55 ~ +85°C 5 cycles.	MIL-STD-1344	-	-	-	○	-
13	DURABILITY UNIT CONTACT	Must be less than the std. value after 30 insertion and extraction cycles at the condition described in above item No.4.	MIL-STD-1344	-	30	mΩ	○	-
	CONTACT			-	-	mΩ	-	-
14	SALT SPRAY (CORROSION).	Must not have heavy corrosion after x salt water spray for hours.		-	-	-	-	-
15	H ₂ S-EXPOSURE	Must not have heavy corrosion after ppm for hours.		-	-	-	-	-
16	SO ₂ -EXPOSURE	Must not have heavy corrosion after ppm for hours.		-	-	-	-	-

Notes:1
This temperature includes a rise by heat's generation of connector when electricity passes.

REMARKS	APPROVED	<i>H. Yamamoto</i>	94.3.25	ISSUED BY
	REVIEWED		.	
	CHECKED	J. Oma	94.3.25	
	DESIGNED	M. Gotoh	94.3.24	
	DRAWN	M. Gotoh	94.3.24	

DRAWING No.	SPECIFICATION SHEET		PART No.
SLC4-160092-02			DF1B-X-DS-2.5RC
			CODE No. 0600 4
			CL541-0650-2-

NOTE QT:Qualification Test AT:Assurance Test O:Applicable item FORM No.

TO