





Applicable standard					
Rating	Operating temperature range	-55°C to + 85°C(Note 1)		Storage temperature range	-10°C to + 60°C(Note 3)
	Operating humidity range	20% to 80%(Note 2)		Storage humidity range	40% to 70% (Note 3)
	Voltage	1000V AC/DC		Applicable cable	AWG14 to 16
	Current (*1) rating	AWG14:18A/pin, AWG16:15A/pin		Applicable contact 	DF22 (A) -1416PC (F) A
	Voltage Rating	Current Rating		Overvoltage Category	IP- Degree
UL	600V AC/DC	AWG14:23A/pin, AWG16:21A/pin(Note 4)		—	—
C-UL	600V AC/DC	See table above left(*1) (Temp. rise up 30°C MAX)		—	—
TUV	600V AC/DC	See table above left(*1)		II	IP00
Specifications					
Item		Test method		Requirements	QT AT
Construction					
General examination		Visually and by measuring instrument.		According to drawing.	X X
Marking		Confirmed visually.			X X
Electric characteristics					
Insulation resistance		1000V DC.		1000MΩ MIN.	X —
Voltage proof		2500V AC for 1 min.		No flashover or breakdown.	X —
Mechanical characteristics					
Mechanical operation		30 times insertions and extractions.		No damage, crack or looseness of parts.	X —
Vibration		Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 2 h, for 3 directions.			X —
Shock		490 m/s ² duration of pulse 11 ms at 3 times for 3 directions.			X —
Environmental characteristics					
Rapid change of temperature		Temperature -55→ 5 to 35→+85→ 5 to 35 °C Time 30→ 5 max → 30→ 5 max min Under 5 cycles.		1) Insulation resistance: 1000MΩ MIN. 2) No damage, crack or looseness of parts.	X —
Damp heat (Steady state)		Exposed at 40 ± 2 °C, 90 to 95 %, 96 h.		1) Insulation resistance: 500MΩ MIN. 2) No damage, crack or looseness of parts.	X —
Remarks					
Note 1:Include the temperature rising by current.					
Note 2:No condensing.					
Note 3:Applicable to unused product packaging.					
Note 4:Indicates the current that corresponds to the RTI value (temperature at which performance is halved) of the resin when the ambient temperature is 25°C.					
	Count	Description of revisions	Designed	Checked	Date
	1	DIS-H-00008679	TS. KUMAZAWA	SZ. ONO	20210407
Unless otherwise specified , refer to IEC 60512.				Approved	HS. OKAWA 20170822
				Checked	TS. FUKUSHIMA 20170822
				Designed	MI. SAKIMURA 20170822
				Drawn	MI. SAKIMURA 20170822
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing no.	ELC-163601-00-00	
	Specification sheet		Part no.	DF22L-2EP-7. 92C	
	Hirose electric co., ltd.		Code no.	CL0680-1064-6-00	 1/1