

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				..	△				..
△				..	△				..
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-30℃ TO +85℃ (NOTE1)			STORAGE TEMPERATURE RANGE	-10℃ TO +60℃			
	VOLTAGE	250 V DC			APPLICABLE CONTACT	—			
	CURRENT	3 A			APPLICABLE CONNECTOR	—			
					APPLICABLE CABLE	UL1061 24 AWG TO 28AWG			
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			Q	T A T
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			○	○
MARKING		CONFIRMED VISUALLY.						○	○
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).			30 mΩ MAX.			○	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD.		20 mV MAX. mA (DC OR 1000 Hz).			mΩ MAX.			—	—
INSULATION RESISTANCE		500 V DC			1000 MΩ MIN.			○	—
VOLTAGE PROOF		650 V AC FOR 1 min			NO FLASHOVER OR BREAKDOWN.			○	—
MECHANICAL CHARACTERISTICS									
CONTACT INSERTION AND EXTRACTION FORCES		BY STEEL GAUGE.			INSERTION FORCE N MAX. EXTRACTION FORCE N MIN.			—	—
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE N MAX. EXTRACTION FORCE N MIN.			—	—
MECHANICAL OPERATION		TIMES INSERTIONS AND EXTRACTIONS			① CONTACT RESISTANCE: mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			—	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm. — m/s ² AT 2 h FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF μs. ② CONTACT RESISTANCE: — mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○	—
SHOCK		AT m/s ² DURATION OF PULSE TIMES FOR DIRECTIONS. ms			① NO ELECTRICAL DISCONTINUITY OF μs. ② CONTACT RESISTANCE: mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			—	—
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2℃, 90~95%, 96 h.			① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→5~35, +85→5~35℃ TIME 30→5→30→5 min UNDER 5 CYCLES.			① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○	—
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, IMMERSION, DURATION, s. °C FOR			NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.			—	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, FOR IMMERSION DURATION, s. °C			A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.			—	—
REMARKS									
NOTE1 INCLUDE THE TEMPERATURE RISING BY CURRENT.				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
Unless otherwise specified, refer to MIL-STD-1344.				T. Miyazaki 95.4.17	T. Miyazaki 95.4.17	J. Oma 95.4.18	M. Yamano 95.4.18		
Note QT: Qualification Test AT: Assurance Test ○: Applicable Test									
HRS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO. DF4-※DP-2C		
CODE NO. (OLD) CL		DRAWING NO. ELC4-160366			CODE NO. 0078-3 C L 544-0092-4			1/1	