







Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




Recommended panel cut out dimension



Mating figure




Note 1. Per pack : 100 pieces.

				1	PBT	Red. UL94V-0			
NO.	MATERIAL	FINISH . REMARKS			NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : KI. AKIYAMA		15.08.27	DRAWING NO.		EDC-360512-15-00		
		CHECKED : TS. FUKUSHIMA		15.08.27	PART NO.		DF60-1EP-10.16C(15)		
		DESIGNED : TS. KUMAZAWA		15.08.27	CODE NO.		CL680-3050-2-15		
		DRAWN : TS. KUMAZAWA		15.08.27			 1/2		


Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DF60 In-Line type recommended panel mounting Manual (When nuts uses)


Nut installation process



1. Slide a nut (Size:M3) to nut fix part.




2. Press down the nut until it clicks.
Then this sound means the nut has inserted
into nut holder.




Panel mounting process

1. Insert connector into panel cut out part.



2. Tighten a screw (Size:M3) to fix with panel.
Recommended torque : Less than 49N · cm



HRS

DRAWING NO.	EDC-360512-15-00
PART NO.	DF60-1EP-10.16C(15)
CODE NO.	CL680-3050-2-15

2/2