




- ⚠ Note 1. Applicable wire : 26 to 30 AWG
Outer diameter : $\phi 0.56$ to 1.0mm
2. 1 reel:10000 contacts.
- ③ Style of reel and box are shown in figure.
- ① 4. A maximum of 5 reels are packed up in one box.
- ① 5. Please be sure to check the form of crimping using a cable when you adjust applicator.
- ① 6. Refer to the technical specification(ATAP-H0373-00)for the packing type.

0.15 ± 0.05

				1	Phosphor bronze	Contact area:Gold plating 0.2μm min Crimping area:Tin plating 1μm min Carrier area:Tin plating 1μm min Others:Nickel plating 0.5μm min							
NO.		MATERIAL		FINISH . REMARKS		NO.		MATERIAL		FINISH . REMARKS			
UNITS mm				SCALE 20 : 1				COUNT 9	DESCRIPTION OF REVISIONS DIS-H-00004839		DESIGNED HT. SATO	CHECKED SZ. ONO	DATE 20190513
 HIROSE ELECTRIC CO., LTD.				APPROVED		TS. SAKATA		20091027		DRAWING NO. EDC-162290-00-01			
				CHECKED		TS. FUKUSHIMA		20091027		PART NO. DF13G-2630SCFA			
				DESIGNED		KT. ISHII		20091013		CODE NO. CL536-0642-9-00			
				DRAWN		YK. NAKATSU		20091007		 1/1			