








RECOMMENDED PC BOARD PATTERN



PANEL CUOUT

(PANEL THICKNESS : 1.6mm MAX)



- NOTES 1 This product must be screwed to the board.
Please prepare the screws by the customer.
<SCREW REQUIREMENTS>
NOMINAL DIAMETER: M2.6 x 0.45
SCREW LENGTH : 1.8 ± 0.45 + BOARD thickness 't'

3	PBT	UL94V-0(BLACK)			
2	PBT	UL94V-0(BLACK)	5	STEEL	NICKEL PLATING
1	PHOSPHOR BRONZE	SELECTIVE GOLD PLATING 0.3 μm	4	ZINC ALLOY DIE CASTING	NICKEL PLATING
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT 3	DESCRIPTION OF REVISIONS DIS-E-00010989	DESIGNED KG. OKITA
HIROSE ELECTRIC CO., LTD.		APPROVED : H0. MIWA	20050105	DRAWING NO.	EDC3-044249-01
		CHECKED : YH. ENAMI	20050105	PART NO.	DX20M-14S(50)
		DESIGNED : TU. TANIGUCHI	20050105	CODE NO.	CL0230-5012-5-50
		DRAWN : TU. TANIGUCHI	20050105		
					1/1