Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					

APPLICABLE STANDARD

RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTE1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	100V AC	APPLICABLE CONTACT	—
	CURRENT	AWG28: 1 A, 30AWG: 0.5 A	APPLICABLE CONNECTOR	DF19G-8P-1H
		32AWG : 0.3 A	APPLICABLE CABLE	OUTER DIAMETER: φ0.5 TO 0.6 mm

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	○	○
MARKING	CONFIRMED VISUALLY.		○	○
ELECTRICAL CHARACTERISTICS				
CONTACT RESISTANCE	mA (DC OR 1000 Hz).	mΩ MAX.	—	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV MAX. mA(DC OR 1000 Hz).	mΩ MAX.	—	—
INSULATION RESISTANCE	100V DC.	500 MΩ MIN.	○	—
VOLTAGE PROOF	300V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	○	—
MECHANICAL CHARACTERISTICS				
CONTACT INSERTION AND EXTRACTION FORCES	BY STEEL GAUGE.	INSERTION FORCE N MAX. EXTRACTION FORCE N MIN.	—	—
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE N MAX. EXTRACTION FORCE N MIN.	—	—
MECHANICAL OPERATION	TIMES INSERTIONS AND EXTRACTIONS.	①CONTACT RESISTANCE: mΩ MAX. ②NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	—	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	①NO ELECTRICAL DISCONTINUITY OF 1 μs.	○	—
SHOCK	490 m/s² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	②CONTACT RESISTANCE: - mΩ MAX. ③NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	○	—
ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5~35→ +85→ 5~35 °C TIME 30→ 2~3 → 30→ 2~3 min UNDER 5 CYCLES.	①CONTACT RESISTANCE: 30 mΩ MAX. ②INSULATION RESISTANCE: 500 MΩ MIN. ③NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	○	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2°C, 90~95%, 96h.	①CONTACT RESISTANCE: 30 mΩ MAX. ②INSULATION RESISTANCE: 500 MΩ MIN. ③NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	○	—
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, °C, FOR. IMMERSION, DURATION, s.	NO DEFORMATION ON CASE OR EXCESSIVE LOOSENESS OF THE TERMINALS.	—	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, °C FOR IN IMMERSION, DURATION, s.	SOLDER SHALL COVER A MINIMUM OF % OF THE SURFACE BEING IMMERSED.	—	—

REMARKS
NOTE 1: INCLUDE THE TEMPERATURE RISING BY CURRENT.

Unless otherwise specified, refer to MIL-STD-1344.

DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
H. Umehara	H. Umehara	T. Ono	K. Katayose	
99.5.27	99.5.27	99.5.31	'99.6.1	

Note QT:Qualification Test AT:Assurance Test ○:Applicable Test

HRS HIROSE ELECTRIC CO., LTD. | SPECIFICATION SHEET | PART NO. DF19-8S-1C

CODE NO.(OLD)	DRAWING NO	CODE NO.	
CL	ELC4-162994	CL 685-0029-1	1/1

FORM No.231-1

TO

NC