


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT








RECOMMENDED PCB PATTERN




A(20:1)





HRS DRAWING FOR REFERENCE

NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250℃
OVER 230℃ : 20~40s
PREHEAET : 150~180℃
90~120s △2
2. TEMPERATURE FOR SOLDERING IRON
:280~300℃ WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



MATED CONNECTORS





NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min	6	POLYESTER	
2	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min	5	POLYSTYRENE	
1	PA	BLACK UL94V-0	4	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△2	2	DIS-T-00003979	YONGMUN LEE	HH. TSUKUMO	20181119


HIROSE ELECTRIC CO., LTD.

APPROVED	HK. UMEHARA	20180809	DRAWING NO. EDC-368629-00-00
CHECKED	HH. TSUKUMO	20180809	PART NO. ZE05-8DP-2H
DESIGNED	YH. MAMADA	20180809	
DRAWN	NF. IKEDA	20180808	CODE NO. CL752-2103-0-00 △2 1/2


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKING STYLE

PACKING STYLE DRAWING




REEL DIMENSION (FREE)



300 PCS/REEL

CARDBOARD DIMENSION (FREE)

W=(405) (mm)
D=(405) (mm)
H= (51) (mm)



HRS DRAWING FOR REFERENCE

HRS	DRAWING NO.	EDC-368629-00-00
	PART NO.	ZE05-8DP-2H
	CODE NO.	CL752-2103-0-00