

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	VOLTAGE	200 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %.	
	CURRENT	1 A	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING		CONFIRMED VISUALLY.		x	x
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).	15 mΩ MAX.	x	—
INSULATION RESISTANCE		500 V DC	1000 MΩ MIN.	x	—
VOLTAGE PROOF		650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	x	—
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES		□0.5±0.002mm BY STEEL GAUGE.	INSERTION FORCE: 2.45 N MAX. EXTRACTION FORCE: 0.24 N MIN.	x	—
MECHANICAL OPERATION		100 TIMES INSERTIONS AND EXTRACTIONS.	①CONTACT RESISTANCE: 20 mΩ MAX. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTIONS.	①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		x	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.	①CONTACT RESISTANCE: 20 mΩ MAX. ②INSULATION RESISTANCE:1000 MΩ MIN.	x	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15~+35→+85→+15~+35°C TIME 30 → 5 MAX → 30 → 5 MAX min. UNDER 5 CYCLES.	③NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	①CONTACT RESISTANCE: 20 mΩ MAX. ②NO HEAVY CORROSION.	x	—
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JEIDA - 39)		x	—
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING :250 °C MAX, 220 °C MIN, FOR 60 s 2) SOLDERING IRON :360 °C, FOR 5 s	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245±3°C, FOR IMMERSION DURATION, 3 s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.	x	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.			APPROVED	HS. OKAWA	09. 04. 10
			CHECKED	HT. YAMAGUCHI	09. 04. 10
			DESIGNED	SY. KAMIGA	09. 04. 08
			DRAWN	HK. SUNADORI	09. 04. 08
Unless otherwise specified, refer to MIL-STD-1344.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-082683-21	
HRS	SPECIFICATION SHEET		PART NO.	A3A-32DA-2SV (71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL621-1154-0-71	△ 1/1