

Technical drawing of a mechanical part, likely a valve or connector, showing multiple views and dimensions.

Views:

- Top View:** Shows the overall shape with dimensions 15.7 (total length) and 7.2 (distance from left face to start of threads).
- Front View:** Shows the profile of the part with a central threaded section. A dimension of 15.7 is indicated for the total length.
- Side View:** Shows the profile of the part with a central threaded section. A dimension of 15.7 is indicated for the total length.
- Section A-A:** A cross-section view showing a U-shaped profile with a width of (2.6) and a height of (2.7).
- Section B-B:** A cross-section view showing a U-shaped profile with a width of (3) and a height of (3).

Dimensions:

- 15.7 (Total length)
- 7.2 (Distance from left face to start of threads)
- 15.7 (Total length)
- (2.6) (Width of Section A-A)
- (2.7) (Height of Section A-A)
- (3) (Width of Section B-B)
- (3) (Height of Section B-B)

Notes:

- 1 (Reference to the threaded section)
- 1R5 (Thread specification)
- Pb FREE (Lead-free material)