

Mar. 1. 2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
<b>APPLICATION STANDARD</b>									
<b>RATING</b>	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C			STORAGE TEMPERATURE RANGE	--- °C TO --- °C			
	VOLTAGE	200V AC			OPERATING HUMIDITY RANGE	--- % TO --- %			
	CURRENT	2 A			APPLICABLE CABLE	AWG#26~36			
<b>SPECIFICATIONS</b>									
<b>ITEM</b>		<b>TEST METHOD</b>			<b>REQUIREMENT</b>			<b>QT AT</b>	
<b>CONSTRUCTION</b>									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING			X	X
MARKING		CONFIRMED VISUALLY						X	X
<b>ELECTRICAL CHARACTERISTICS</b>									
INSULATION RESISTANCE		500 V DC			1000 MΩ MIN.			X	-
VOLTAGE PROOF		650 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN			X	-
<b>ENVIRONMENTAL CHARACTERISTICS</b>									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C. 90~95 %, 96 h.			1)INSULATION RESISTANCE: 1000 MΩ MIN.			X	-
RAPID CHAGE OF TEMPERTURE		TEMPERTURE-55→15~35→ 85→15~35°C TIME 30→10~15→ 30 → 10~15 min. UNDER 5 CYCLES.			2) NO DAMAGE, CRACK AND LOOSENESS OF PART.			X	-
<b>REMARKS</b>									
				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				M.ISHIZUKA 99.09.25	H. Okawa 99.09.25	<i>M. Yamaguchi</i> 99.09.25	<i>M. Yamaguchi</i> 99.09.25		
UNLESS OTHERWISE SPECIFIED, REFER TO MIL-STD-1344									
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST									
<b>HRS</b> HIROSE ELECTRIC CO.,LTD.				<b>SPECIFICATION SHEET</b>			PART NO. <b>A3B - 24D - 2C</b>		
CODE NO.(OLD)		DRAWING NO.			CODE NO.		1		
CL		ELC4 - 021400			CL 621 - 0313 - 6		1		

TO
PCK