

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO +105 °C (NOTE1)	STORAGE TEMPERATURE RANGE	-40 °C TO +105 °C	
	VOLTAGE	250 V AC	CURRENT	1 A	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	x x
MARKING		CONFIRMED VISUALLY.			x x
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		1A DC.		CENTER CONTACT: 30 mΩ MAX. OUTER CONTACT: 60 mΩ MAX.	x —
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV AC MAX, 0.1 mA(OR 1kHz)		CENTER CONTACT: 30 mΩ MAX. OUTER CONTACT: 60 mΩ MAX.	x —
INSULATION RESISTANCE		500 V DC		100 MΩ MIN.	x —
VOLTAGE PROOF		650 V AC FOR 1 MIN.		NO FLASHOVER OR BREAKDOWN.	x —
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES		φ4.5 BY STEEL GAUGE.		INSERTION FORCE 29.4 N MAX. WITHDRAWAL FORCE 2.9 N MIN.	x —
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.		① CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	x — x
VIBRATION		FREQUENCY 20 TO 200 Hz, 43.1m/s <sup>2</sup> , AT 3h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	x x x —
SHOCK		FREQUENCY 20 TO 50 Hz, 66.6m/s <sup>2</sup> AT 1 h.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	x x x —
LOCK STRENGTH		APPLYING A PULL FORCE THE MATING AXIALLY AT 98N MAX.		① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.	x — x
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 60°C, 90 TO 95%, 500h.		① CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	x x x —
RAPID CHANGE OF TEMPERATURE		TEMPERATURE:-40→5 TO 35→85→5 TO 35°C TIME: 30→5→30→5 MIN UNDER 1000 CYCLES.		① CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	x x x —
DRY HEAT		EXPOSED AT 105°C, 300h.		① CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	x x —
COLD		EXPOSED AT -55°C, 120h.		① CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	x x —
RESISTANCE TO HSO <sub>3</sub> GAS		EXPOSED IN 500 PPM FOR 8h.		① CENTER CONTACT: 60 mΩ MAX. OUTER CONTACT: 120 mΩ MAX.	x —
RESISTANCE TO SOLDERING HEAT		TOP OF IRON 350°C, 10 sec.		NO DEFORMATION IN CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x —
SOLDERABILITY		TOP OF IRON 350°C, 3 sec.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	x —
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△0					
REMARK			APPROVED	NH.NAKATA	15.09.03
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.			CHECKED	KI.HIROKAWA	15.09.03
(NOTE2) RECOMMENDED PCB THICKNESS: 1.6mm.			DESIGNED	ming.jiang	15.08.24
			DRAWN	ming.jiang	15.08.24
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-166308-00-00
HRS	SPECIFICATION SHEET		PART NO.	GT16C-1P-DS (A)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL766-0062-7-00	△0 1/1