

Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO 105 °C (NOTE1)	STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C
	VOLTAGE	250 V AC	CURRENT	3 A
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.		x	x
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	1A DC.	SIGNAL : 30 mΩ MAX .	x	-
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	SIGNAL : 30 mΩ MAX .	x	-
INSULATION RESISTANCE	500 V DC	100 MΩ MIN.	x	-
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	x	-
MECHANICAL CHARACTERISTICS				
CONTACT INSERTION AND EXTRACTION FORCES	12.3 × 9 BY STEEL GAUGE.	INSERTION FORCE 6.5 N MAX. EXTRACTION FORCE 0.1~6.5 N .	x	-
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE : 60 mΩ MAX . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
VIBRATION	FREQUENCY 20 TO 200 Hz, 43.1 m/s ² AT 3 h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE : 60 mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
SHOCK	FREQUENCY 20 TO 50 Hz, 66.6 m/s ² AT 1 h .	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE : 60 mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
LOCK STRENGTH	APPLYING A PULL FORCE THE MATING AXIALLY AT 98N MAX.	① DURING APPLYING, MATING COMPLETELY. ② AFTER APPLYING, NO DEFECT OF MATING PARTS.	x	-
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.	① CONTACT RESISTANCE : 60 mΩ MAX . ② INSULATION RESISTANCE : 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-40→5 TO 35→ 85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE : 60 mΩ MAX . (NOTE3) ② INSULATION RESISTANCE : 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-
DRY HEAT	EXPOSED AT 105°C, 300 h.	① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.	x	-
COLD	EXPOSED AT -55°C, 120 h.	① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.	x	-
CORROSION, SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 96 h.	① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.	x	-
RESISTANCE TO HSO ³ GAS	EXPOSED IN 500 PPM FOR 8 h.	① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.	x	-
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, 260 °C FOR IMMERSION, DURATION, 10 s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	-
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245 °C FOR IMMERSION DURATION, 3 s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	x	-
	①			
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
①	2 DIS-T-001222	TS. KUBOTA	NH. NAKATA	09.04.14
REMARK		APPROVED	KS. SATOH	05.01.05
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.		CHECKED	NH. NAKATA	05.01.05
(NOTE2) APPLICABLE BOARD : 1.6±0.2		DESIGNED	NA. HARUBAYASHI	05.01.05
(NOTE3) OVER 500 CYCLES : 120 mΩ MAX .(OUTER CONTACT ONLY)		DRAWN	TK. SHISHIKURA	05.01.05
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO. ①		ELC4-165532-01
HRS	SPECIFICATION SHEET	PART NO.	GT17V-10DP-DS (70)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL767-0034-8-70	① 1/1