

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-30 °C TO 105 °C (NOTE1)	STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C		
	VOLTAGE	250 V AC	CURRENT	3 A		
SPECIFICATIONS						
ITEM	TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×
MARKING	CONFIRMED VISUALLY.				×	×
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE	1A DC.		SIGNAL : 30 mΩ MAX .		×	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)		SIGNAL : 30 mΩ MAX .		×	—
INSULATION RESISTANCE	500 V DC		100 MΩ MIN.		×	—
VOLTAGE PROOF	650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		×	—
MECHANICAL CHARACTERISTICS						
CONTACT INSERTION AND EXTRACTION FORCES	12.3 × 9 BY STEEL GAUGE.		INSERTION FORCE 6.5 N MAX. EXTRACTION FORCE 0.1~6.5 N .		×	—
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE : 60 mΩ MAX . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—
VIBRATION	FREQUENCY 20 TO 200 Hz, 43.1 m/s <sup>2</sup> AT 3 h FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE : 60 mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—
SHOCK	FREQUENCY 20 TO 50 Hz, 66.6 m/s <sup>2</sup> AT 1 h .		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE : 60 mΩ MAX . ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—
LOCK STRENGTH	APPLYING A PULL FORCE THE MATING AXIALLY AT 98N MAX.		① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.		×	—
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.		① CONTACT RESISTANCE : 60 mΩ MAX . ② INSULATION RESISTANCE : 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-40→5 TO 35→ 85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE : 60 mΩ MAX . (NOTE3) ② INSULATION RESISTANCE : 100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	—
DRY HEAT	EXPOSED AT 105°C, 300 h.		① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.		×	—
COLD	EXPOSED AT -55°C, 120 h.		① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.		×	—
CORROSION, SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 96 h.		① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.		×	—
RESISTANCE TO HSO <sup>3</sup> GAS	EXPOSED IN 500 PPM FOR 8 h.		① CONTACT RESISTANCE : 60 mΩ MAX . ② NO HEAVY CORROSION.		×	—
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, 260 °C FOR IMMERSION, DURATION, 10 s.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		×	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245 °C FOR IMMERSION DURATION, 3 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.		×	—
	△					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△	2	DIS-T-001222	TS. KUBOTA	NH. NAKATA	09. 04. 14	
REMARK			APPROVED	KS. SATOH	05. 01. 05	
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.			CHECKED	NH. NAKATA	05. 01. 05	
(NOTE2) APPLICABLE BOARD : 1.6±0.2			DESIGNED	NA. HARUBAYASHI	05. 01. 05	
(NOTE3) OVER 500 CYCLES : 120 mΩ MAX .(OUTER CONTACT ONLY)			DRAWN	TK. SHISHIKURA	05. 01. 05	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO. △		ELC4-165532-01	
HRS	SPECIFICATION SHEET		PART NO.	GT17V-10DP-DS (70)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL767-0034-8-70 △ 1/1		