

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C (NOTE1)		STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C
	VOLTAGE	250 V AC		CURRENT	$\triangle 2$ 1 A
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ELECTRIC CHARACTERISTICS					
$\triangle 2$	CONTACT RESISTANCE	1A DC.		$\triangle 2$ SIGNAL:30 m Ω MAX, SHIELD:60m Ω MAX.	X —
$\triangle 2$	CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)		$\triangle 2$ SIGNAL:30 m Ω MAX, SHIELD:60m Ω MAX.	X —
$\triangle 2$	INSULATION RESISTANCE	500 V DC		100 M Ω MIN.	X —
$\triangle 2$	VOLTAGE PROOF	650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X —
MECHANICAL CHARACTERISTICS					
	CONTACT INSERTION AND EXTRACTION FORCES	BY STEEL GAUGE, —.		INSERTION FORCE — N MAX. EXTRACTION FORCE — N MIN.	— —
	MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS. $\triangle 2$		① CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X — X —
	VIBRATION	FREQUENCY 20 TO 200 Hz, 43.1 m/s ² AT 3 h FOR 3 DIRECTIONS. $\triangle 2$		① NO ELECTRICAL DISCONTINUITY OF 10 μ s. ② CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X — X — X —
	SHOCK	FREQUENCY 20 TO 50 Hz, 66.6 m/s ² AT 1 h , FOR 3 DIRECTIONS. $\triangle 2$		① NO ELECTRICAL DISCONTINUITY OF 10 μ s. ② CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X — X — X —
$\triangle 2$	LOCK STRENGTH	APPLYING A PULL FORCE THE MATING AXIALLY AT 78.4N MIN.		① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.	X — X —
ENVIRONMENTAL CHARACTERISTICS					
$\triangle 2$	DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 500 h.		① CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ② INSULATION RESISTANCE:100 M Ω MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X — X — X —
$\triangle 2$	RAPID CHANGE OF TEMPERATURE	TEMPERATURE-40→5 TO 35→85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.		① CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ② INSULATION RESISTANCE:100 M Ω MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X — X — X —
	DRY HEAT	EXPOSED AT 105°C, 300 h. $\triangle 2$		① CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X — X —
	COLD	EXPOSED AT -55°C , 120 h.		① CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X — X —
	RESISTANCE TO SO ₂ GAS $\triangle 2$	EXPOSED IN 500 PPM FOR 8h.		① CONTACT RESISTANCE: SIGNAL:60 m Ω MAX, SHIELD:120m Ω MAX. ② NO HEAVY CORROSION.	X — X —
$\triangle 2$					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
$\triangle 2$	14	DIS-T-002416	MH. SHOUJI	NH. NAKATA	11. 10. 06
REMARK (NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.			APPROVED	KS. SATOH	07. 01. 24
			CHECKED	KS. SATOH	07. 01. 24
			DESIGNED	NA. HARUBAYASHI	07. 01. 23
			DRAWN	NA. HARUBAYASHI	07. 01. 23
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-166640-00
HRS	SPECIFICATION SHEET		PART NO.	GT17HS-4S-5CF	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL767-0135-5-00	$\triangle 2$ 1/1