

Feb. 1. 2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)			STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C			
	VOLTAGE	150 V AC			APPLICABLE CONTACT	—			
	CURRENT	1 A			APPLICABLE CONNECTOR	DF13-*DP-1.25C			
					APPLICABLE CABLE	—			
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			<input type="radio"/>	<input type="radio"/>
MARKING		CONFIRMED VISUALLY.						<input type="radio"/>	<input type="radio"/>
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).			30 mΩ MAX.			<input type="radio"/>	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, mA(DC OR 1000 Hz).						—	—
INSULATION RESISTANCE		100 V DC.			500 MΩ MIN.			<input type="radio"/>	—
VOLTAGE PROOF		500 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.			<input type="radio"/>	—
MECHANICAL CHARACTERISTICS									
CONTACT INSERTION AND EXTRACTION FORCES		<input type="checkbox"/> 0.35 ± 0.002 BY STEEL GAUGE.			INSERTION FORCE 3.9 N MAX. EXTRACTION FORCE 0.3 N MIN.			<input type="radio"/>	—
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE ——— N MAX. EXTRACTION FORCE ——— N MIN.			—	—
MECHANICAL OPERATION		30 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			<input type="radio"/>	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, - m/s ² AT 2 h, FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 1 μs.			<input type="radio"/>	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			② CONTACT RESISTANCE: - mΩ MAX. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			<input type="radio"/>	—
ENVIRONMENTAL CHARACTERISTICS									
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → 5 ~ 35 → +85 → 5 ~ 35 °C TIME 30 → 10 → 30 → 10 min UNDER 5 CYCLES.			① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			<input type="radio"/>	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 ~ 95 %, 96 h.			① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			<input type="radio"/>	—
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, °C, FOR IMMERSION, DURATION, s.			NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.			—	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, °C FOR IMMERSION DURATION, s.			SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.			—	—
REMARKS NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT.					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
					<i>H. Umehara</i>	<i>H. Umehara</i>	<i>J. Ona</i>	<i>M. Yamamoto</i>	
					197.3.3	197.3.3	97.3.4	97.3.4	
Unless otherwise specified, refer to MIL-STD-1344.									
Note QT:Qualification Test AT:Assurance Test ○:Applicable Test									
HRS HIROSE ELECTRIC CO., LTD.					SPECIFICATION SHEET			PART NO. DF13-*DS*-1.25C	
CODE NO.(OLD) CL		DRAWING NO. ELC4-160109-03			PART NO. CL		536		1/1

TO

