





Dec.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING 	OPERATING TEMPERATURE RANGE	-35°C TO +85°C(NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C(NOTE 3)	
	OPERATING HUMIDITY RANGE	40% TO +80%(NOTE 2)	STORAGE HUMIDITY RANGE	40% TO +70%(NOTE 3)	
	VOLTAGE	100V AC/DC	APPLICABLE CONNECTOR	DF19-*S-1C DF19G-*S-1C(05)	
	CURRENT	30 AWG : 0.9 A/PIN 32 AWG : 0.8 A/PIN	APPLICABLE CABLE	30-32 AWG	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	20 mV MAX, 1 mA(DC or 1000Hz).	30 mΩ MAX.	X	-	
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES	0.2 mm BY STEEL GAUGE	INSERTION FORCE : 3 N MAX EXTRACTION FORCE : 0.2 N MIN	X	-	
MECHANICAL OPERATION	30 TIMES INSERTION AND EXTRACTION.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs.	X	-	
SHOCK	490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
ENVIRONMENTAL CHARACTERISTICS 					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→-5 TO 35→+85 →5 TO 35 °C TIME 30→2 TO 3 → 30 →2 TO 3 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.		X	-	
OTHERS 					
CRIMP TENSILE STRENGTH(NOTE4)	APPLY WIRE TENSILE STRENGTH TO CAULKING AREA AXIALLY UNTIL WIRE BECOME LOOSEN OR BREAKDOWN.	① 30 AWG (7/φ 0.102 mm) : 8 N MIN ② 32 AWG (7/φ 0.08 mm) : 5 N MIN	X	-	
REMARKS NOTE1:INCLUDE THE TEMPERATURE RISING BY CURRENT. NOTE2:NO CONDENSING. NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE HARNESS ASSEMBLY. AFTER HARNESS ASSEMBLY, OPERATION TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION. NOTE4:APPLICABLE WHEN THE CABLE CORE IS TIN-PLATED COPPER WIRE.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	3	DIS-H-00005721	HK. HAYASHI	HS. OKAWA	20200212
Unless otherwise specified, refer to IEC 60512.			APPROVED	TY. OMA	20060519
			CHECKED	HK. UMEHARA	20060518
			DESIGNED	AH. MIYAZAKI	20060518
			DRAWN	AH. MIYAZAKI	20060518
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-164752-00-01	
	SPECIFICATION SHEET		PART NO.	DF19A-3032SCFA	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL685-0046-0-00	 1/1