Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C(1)	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C(2)
	VOLTAGE	200 V AC	OPERATING HUMIDITY RANGE	40 % TO 80 %
	CURRENT	3 A	STORAGE HUMIDITY RANGE	40 % TO 70 %(2)

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	15 mΩ MAX.	×	
INSULATION RESISTANCE	500 V DC.	1000 MΩ MIN.	×	
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.	①CONTACT RESISTANCE: 15 mΩ MAX. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
VIBRATION	FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTION.	①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
SHOCK	490 m/s^2, DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		×	
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ～ 95 %, 96 h.	①CONTACT RESISTANCE: 15 mΩ MAX. ②INSULATION RESISTANCE: 1000 MΩ MIN.	×	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-65→+15～+35→+125→+15～+35°C TIME 30 → 10～15 → 30 → 10～15 min UNDER 5 CYCLES.	③NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	①CONTACT RESISTANCE: 15 mΩ MAX. ②NO HEAVY CORROSION.	×	
HYDROGEN SULPHIDE	EXPOSED IN 3 PPM FOR 96 h. (TEST STANDARD:JEIDA-38)		×	
RESISTANCE TO SOLDERING HEAT	1) SOLDER BATH:SOLDER TEMPERATURE, 260±5℃ FOR IMMERSION,DURATION,10±1s. 2) SOLDERING IRONS : 350℃ FOR 3 s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL	×	
SOLDRABILITY	SOLDERED AT SOLDER TEMPERATURE 245±3℃ FOR IMMERSION DURATION, 2s.	A NEW UNIFORM COATING OF SOLDER SHALL OVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
⚠					

REMARK (1) TEMPERATURE RISE INCLUDED WHEN ENERGIZED.
(2) THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.

Unless otherwise specified, refer to MIL-STD-1344.

APPROVED	HS.OKAWA	05.10.11
CHECKED	HS.OZAWA	05.10.07
DESIGNED	KT.DOI	05.10.07
DRAWN	AK.SUZUKAWA	05.10.06

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-018389-21

HRS SPECIFICATION SHEET — PART NO. A2-*PA-2.54DSA(71)

HIROSE ELECTRIC CO., LTD. — CODE NO. — ⚠0 — 1/1

FORM HD0011-2-1