

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾
	VOLTAGE	200 V AC		OPERATING HUMIDITY RANGE	40 % TO 80 %.
	CURRENT	1 A		STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	× ×
MARKING		CONFIRMED VISUALLY.			× ×
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		15 mΩ MAX.	× -
INSULATION RESISTANCE		500 V DC		1000 MΩ MIN.	× -
VOLTAGE PROOF		650 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	× -
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCES		□0.5±0.002mm BY STEEL GAUGE.		INSERTION FORCE: 2.45 N MAX. EXTRACTION FORCE: 0.24 N MIN.	× -
MECHANICAL OPERATION		100 TIMES INSERTIONS AND EXTRACTIONS.		①CONTACT RESISTANCE: 20 mΩ MAX. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	× -
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTIONS.		①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	× -
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			× -
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		①CONTACT RESISTANCE: 20 mΩ MAX. ②INSULATION RESISTANCE:1000 MΩ MIN.	× -
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15~+35→+85→+15~+35°C TIME 30 → 5 MAX → 30 → 5 MAX min. UNDER 5 CYCLES.		③NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	× -
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		①CONTACT RESISTANCE: 20 mΩ MAX. ②NO HEAVY CORROSION.	× -
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JEIDA - 39)			× -
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING :250 °C MAX, 220 °C MIN, FOR 60 s 2) SOLDERING IRON :360 °C, FOR 5 s		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	× -
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245±3°C, FOR IMMERSION DURATION, 3 s.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	× -
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.				APPROVED	HS.OKAWA 06.05.10
				CHECKED	HS.OZAWA 06.05.10
				DESIGNED	KY.NAKAMURA 06.05.10
Unless otherwise specified, refer to MIL-STD-1344.				DRAWN	AK.SUZUKAWA 06.04.18
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-082603-21
HRS	SPECIFICATION SHEET		PART NO.	A3-*DA-2SV (71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL621	△ 1/1