

Sep.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85°C (NOTE1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60°C (NOTE3)	
	OPERATING HUMIDITY RANGE	20% TO 80% (NOTE2)	STORAGE HUMIDITY RANGE	40% TO 70% (NOTE3)	
	APPLICABLE CONNECTOR	DF57H-3S-1.2C(##)	CURRENT	AWG 28 : 2.0A AWG 30 : 1.5A	
	VOLTAGE	100 V AC/DC		AWG 32 : 1.0A AWG 34 : 0.8A	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20mV MAX, 1mA (DC or 1000Hz).		10 mΩ MAX.	X	-
INSULATION RESISTANCE	100 V DC.		100 MΩ MIN.	X	-
VOLTAGE PROOF	500 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	-
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	30 TIMES INSERTION AND EXTRACTION.		①CONTACT RESISTANCE: 20 mΩ MAX. ②NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
CONTACT INSERTION AND EXTRACTION FORCES	IT TAKES OUT AND INSERTS WITH A CONFORMITY CONNECTOR.		①INSERTION FORCE : 20.0N MAX. ②EXTRACTION FORCE: 0.9N MIN.	X	-
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 10 CYCLES FOR 3 DIRECTION.		①NO ELECTRICAL DISCONTINUITY OF 1 μs. ②NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK	ACCELERATION OF 490 m/s ² , 11ms DURATION, SINE HALF-WAVE, 3 CYCLES IN EACH OF THE 3 AXIS.			X	-
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2°C, 90 TO 95 %, 96 h. (AFTER LEAVING THE ROOM TEMPERATURE FOR 1~2h.)		①CONTACT RESISTANCE: 20 mΩ MAX. ②INSULATION RESISTANCE: 100 MΩ MIN. ③NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55°C→ +85°C TIME 30min→ 30min UNDER 5 CYCLES. (THE TRANSFERRING TIME OF THE TANK IS 2~3 min) (AFTER LEAVING THE ROOM TEMPERATURE FOR 1~2h.)		①CONTACT RESISTANCE: 20 mΩ MAX. ②INSULATION RESISTANCE: 100 MΩ MIN. ③NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING «REFLOW TIME» NUMBER OF REFLOW CYCLES : 2 CYCLES MAX. DURATION ABOVE 220 °C, 60 sec. MAX. PEAK TEMPERATURE: 250°C 10 sec. MAX. «PRE-HEAT TIME» PRE-HEAT TEMPERATURE (MIN) :150 °C PRE-HEAT TEMPERATURE (MAX) :180 °C PRE-HEAT TIME (MIN) : 90 sec. PRE-HEAT TIME (MAX) : 120 sec. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE :350±10°C, SOLDERING TIME : 3sec. NO STRENGTH ON CONTACT.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	-
SOLDERABILITY	SOLDERING TEMPERATURE : 245°C DURATION OF IMMERSION :SOLDERING, FOR 5 sec.		NEW UNIFORM COATING OF SOLDER SHALL COVER MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.	X	-
NOTE 1: INCLUDE THE TEMPERATURE RISING BY CURRENT.					
NOTE2:NO CONDENSING					
NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFOR PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITTY RANGE IS APPLIED FOR INTERIM STRAGE DURING TRANSPORTATION.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS			APPROVED	HK. UMEHARA	13. 04. 12
			CHECKED	HK. UMEHARA	13. 04. 12
Unless otherwise specified, refer to JIS C 5402.			DESIGNED	TS. KUMAZAWA	13. 04. 12
			DRAWN	MI. SAKIMURA	13. 04. 12
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-344680-01	
HRS	SPECIFICATION SHEET		PART NO.	DF57H-2P-2. 4V (21)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL666-0109-0-21	△ 1/1