





Dec.1.2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85°C (NOTE1)	STORAGE TEMPERATURE RANGE	-10 °C TO +60°C (NOTE3)		
	OPERATING HUMIDITY RANGE	20% TO 80% (NOTE2)	STORAGE HUMIDITY RANGE	40% TO 70% (NOTE3)		
	APPLICABLE CONNECTOR	DF57H-6S-1.2C(##) DF57AH-6S-1.2C(##)	UL-C-UL RATING 	OPERATING TEMPERATURE RANGE	-35 °C TO +75°C (NOTE1)	
	APPLICABLE CONTACT	DF57-****SCF(##)		VOLTAGE	29 V AC/DC	
	VOLTAGE	50 V AC/DC		CURRENT	26 TO 28 AWG : 1.5A/PIN 30 TO 34 AWG : 1.0A/PIN	
CURRENT	26 TO 28 AWG : 1.5A/PIN 30 AWG : 1.0A/PIN 32 AWG : 0.8A/PIN 34 AWG : 0.5A/PIN					
SPECIFICATIONS						
ITEM	TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X	X
MARKING	CONFIRMED VISUALLY.				X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20mV MAX, 1mA (DC or 1000Hz).		10 mΩ MAX.		X	-
INSULATION RESISTANCE	100 V DC.		100 MΩ MIN.		X	-
VOLTAGE PROOF	500 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		X	-
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION	30 TIMES INSERTION AND EXTRACTION.		1)CONTACT RESISTANCE: 20 mΩ MAX. 2)NO DAMAGE, CRACK OR LOOSENESS OF PARTS.		X	-
CONTACT INSERTION AND EXTRACTION FORCES	IT TAKES OUT AND INSERTS WITH A CONFORMITY CONNECTOR.		1)INSERTION FORCE : 30.0N MAX. 2)EXTRACTION FORCE: 1.2N MIN.		X	-
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 10 CYCLES FOR 3 DIRECTION.		1)NO ELECTRICAL DISCONTINUITY OF 1 μ s. 2)NO DAMAGE, CRACK OR LOOSENESS OF PARTS.		X	-
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				X	-
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2°C , 90 TO 95 % , 96 h. (AFTER LEAVING THE ROOM TEMPERATURE FOR 1-2h.)		1)CONTACT RESISTANCE: 20 mΩ MAX. 2)INSULATION RESISTANCE: 100 MΩ MIN. 3)NO DAMAGE, CRACK OR LOOSENESS OF PARTS.		X	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55°C → +85°C TIME 30min → 30min UNDER 5 CYCLES. (THE TRANSFERRING TIME OF THE TANK IS 2-3 min) (AFTER LEAVING THE ROOM TEMPERATURE FOR 1-2h.)		1)CONTACT RESISTANCE: 20 mΩ MAX. 2)INSULATION RESISTANCE: 100 MΩ MIN. 3)NO DAMAGE, CRACK OR LOOSENESS OF PARTS.		X	-
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING « REFLOW TIME » NUMBER OF REFLOW CYCLES : 2 CYCLES MAX. DURATION ABOVE 220 °C, 60 sec. MAX. PEAK TEMPERATURE: 250°C 10 sec. MAX. « PRE-HEAT TIME » PRE-HEAT TEMPERATURE(MIN) :150 °C PRE-HEAT TEMPERATURE(MAX) :180 °C PRE-HEAT TIME(MIN) : 90 sec. PRE-HEAT TIME(MAX) : 120 sec. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE :350±10°C, SOLDERING TIME : 3sec. NO STRENGTH ON CONTACT.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		X	-
SOLDERABILITY	SOLDERING TEMPERATURE : 245°C DURATION OF IMMERSION :SOLDERING, FOR 5 sec.		NEW UNIFORM COATING OF SOLDER SHALL COVER MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.		X	-
NOTE1:INCLUDE THE TEMPERATURE RISING BY CURRENT. NOTE2:NO CONDENSING. NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE MOUNTED ON PCB. AFTER MOUNTED ON PCB, OPERATION TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	1	DIS-H-00005763	HK. HAYASHI	SZ. ONO	20200220	
REMARKS			APPROVED	KI. AKIYAMA	20120221	
			CHECKED	HK. UMEHARA	20120221	
Unless otherwise specified, refer to IEC 60512.			DESIGNED	TS. KUMAZAWA	20120220	
			DRAWN	TS. KUMAZAWA	20120220	
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-343908-21-01	
	SPECIFICATION SHEET		PART NO.	DF57H-6P-1.2V (21)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL666-0108-8-21		1/1